Product Details for GPB

No Image Available

GPB

Tyco Part Number: 1423155-1

Active

Control Relays

Not ELV or RoHS Compliant

Product Highlights:

- GP Series
- Power
- DC Actuating System
- Input Voltage = 24 VDC
- Contact Arrangement = 1 Form C, SPDT, 1 C/O

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us
About This Product

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- GP, ML, and TR Series Control Relays (PDF, English)

CAD Files:

- None Available

List all Documents

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Power
- Termination Type = 16 Flat Base Pins

Electrical Characteristics:

- Actuating System = DC
- Input Voltage (VDC) = 24
- Contact Rating = 10A Resistive @ 220 VAC/48 VDC

Body Related Features:

- Series = GP

Contact Related Features:

- Approved Standards = CSA Certified, UL Listed
- Approx. Dimensions (L x W x H) (mm [in]) = 45.00 x 45.00 x 109.00 [1.773 x 1.773 x 4.294]
- Mounting Options = Socket

Configuration Related Features:

- Contact Arrangement = 1 Form C, SPDT, 1 C/O

Industry Standards:

- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

Conditions for Usage:

- Temperature Range (°C) = 0 – 60

Other:

- Brand = Agastat

© 2006 Tyco Electronics Corporation All Rights Reserved