


## 1055692-1 Product Details

 [Share](#)
 [Print](#)
 [Email](#)



**1055692-1**

TE Internal Number: 1055692-1

 **Active**

 [View 3D PDF](#)

### OSMT/SSMT RF Connectors

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- RF Connector Type = OSMT
- Connector Style = Plug
- Slotted Single Direction Cable Entry
- Packaging Method = 330mm Tape & Reel
- RoHS compliant, ELV compliant

[View all Features](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [TAPE AND REEL PACKAGING, OSMT PLUG, 330mm REEL\(2500 ...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version C)
- [3D Model](#) (IGES, Version C)
- [3D Model](#) (STEP, Version C)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- RF Connector Type = OSMT
- Body Style = Straight

#### Body Features:

- Cable Entry = Slotted Single Direction

#### Contact Features:

- Contact Base Material = Copper Alloy
- Contact Finish = Gold over Nickel

#### Housing Features:

- Connector Style = Plug
- Housing Material = PPS

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Applies To = Printed Circuit Board

#### Packaging Features:

- Packaging Method = 330mm Tape & Reel
- Packaging Quantity = 2,500

#### Other:

- Brand = AMP
- Comment = Requires part number 1055886-1 Disengagement Tool.; No engagement tool required.

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

#### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

