

[Skip to content](#)

| |  
  
 | |  
 | |

## • [Products](#)

- [By Type](#)
  - [Connectors](#)
  - [Electromechanical Components](#)
  - [Electronic Modules](#)
  - [Fiber Optics](#)
  - [Filters](#)
  - [Identification & Labeling](#)
  - [Passive Components](#)
  - [Power Sources](#)
  - [RF & Microwave Products](#)
  - [Tooling Products](#)
  - [Touch Screen Displays](#)
  - [Tubing, Molded and Harnessing Products](#)
  - [Wire, Cable and Cable Assemblies](#)
  - [List all product types...](#)
- [By Industry](#)
  - [Aerospace, Defense & Marine](#)
  - [Appliance](#)
  - [Automotive](#)
  - [Communications](#)
  - [Computer & Consumer Electronics](#)
  - [Industrial & Commercial](#)
  - [Instrumentation & Medical](#)
- [By Brand](#)
- [A to Z](#)
- [Product Innovations](#)

## • [Documentation](#)

- [Find Documents & Drawings](#)
- [Find CAD Models](#)
- [SPICE/Electrical Models](#)
- [NAFTA Certificate of Origin](#)
- [White Papers](#)

## • [Resources](#)

- [Check Product Compliance](#)
- [Cross Reference Products](#)
- [Compare Multiple Products](#)
- [Check Distributor Inventory](#)
- [Find Authorized Distributors](#)

## • [My Account](#)

- [Manage My Part Lists](#)
- [Manage My Downloads](#)
- [Sign In](#)
- [Register](#)
- [Subscribe to our monthly newsletter!](#)

## • [Customer Support](#)

[Home](#) > [Products](#) > [By Type](#) > [Power Blade & Receptacle Connectors \(Timer Products\)](#) > [Product Feature Selector](#) > Product Details

# 1326030-6 Product Details

[Live Product Chat](#)

1326030-6

TE Internal Number: 1326030-6

[Active](#)

[View 3D PDF](#)

Timer Contacts

[Always EU RoHS/ELV Compliant](#)

[\(Statement of Compliance\)](#)

**Product Highlights:**

- Contact
- Contact Type = USCAR
- Receptacle
- Wire Range = 0.50-0.90<sup>2</sup> [20-18] mm [AWG]
- Insulation Diameter = 1.20 - 4.04 mm

[View all Features](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

**Product Drawings:**

- [2.8mm RECEPTACLE UNSEALED](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- None Available

**Product Specifications:**

- None Available

**Additional Information:**

- [Product Line Information](#)

**Application Specifications:**

- [2.8 mm Terminal System \(Sealed and Unsealed\)](#) (PDF, English)

**Additional Product Images:**

- [Line Drawing](#)

**Instruction Sheets:**

- None Available

**Related Products:**

- [Tooling](#)

**CAD Files:** ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version H1)
- [3D Model](#) (IGES, Version H1)
- [3D Model](#) (STEP, Version H1)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- [Product Type](#) = Contact
- [Gender](#) = Receptacle
- [Insulation Diameter \(mm \[in\]\)](#) = 1.20 – 4.04 [0.047 – 0.161]
- [Tab Fit \(mm \[in\]\)](#) = 2.79 x 0.81 [.110 x .032]
- [Wire/Cable Type](#) = Regular Wire
- [Insulation Support](#) = With
- [Comment](#) = Reverse Reel

**Body Related Features:**

- [Wire Range \(mm \[AWG\]\)](#) = 0.50-0.90<sup>2</sup> [20-18]
- [Single Wire Sealing System](#) = No

**Contact Related Features:**

- [Contact Type](#) = USCAR
- [Contact Base Material](#) = Copper Alloy
- [Contact Mating Area Plating Material](#) = Bright Tin

**Industry Standards:**

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

**Conditions for Usage:**

- [Terminate To](#) = Wire

**Packaging Related Features:**

- [Packaging Method](#) = Tape & Reel

**Other:**

- [GET 0.64 Connector System](#) = No
- [Brand](#) = AMP

[Provide Website Feedback](#) | [Need Help?](#)

[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

© 2009 Tyco Electronics Corporation All Rights Reserved

This list is temporary. The list will not be viewable on another computer and will be deleted within 30 days.

If your browser cookies are cleared, your temporary list will be lost. You can save this list and get all of the My Part List features by becoming a registered user of the Tyco Electronics web site.