


1718489 -1 Product Details

[Share](#) |
 [Print](#) |
 [Email](#)



1718489 -1

TE Internal Number: 1718489 -1

[Active](#)

[View 3D PDF](#)

Multiple Contact Point (MCP) & MCON Contact Systems

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Housing
- ? Receptacle
- ? MCP Series
- ? Standard
- ? 18 Positions

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- ? [AMP MCP 1.5K RECEPTACLE INSERT, 18POS. AMP MCP 1.5K...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? [AMP MCP Interconnection System](#) (PDF, English)

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version A1)
- ? [3D Model](#) (IGES, Version A1)
- ? [3D Model](#) (STEP, Version A1)

[List all Documents](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Housing
- ? Gender = Receptacle
- ? Mating Area Interface Dimensions (mm [in]) = 1.50 [.059]
- ? Sealed = No
- ? Mount Angle = Straight

Mechanical Attachment:

- ? Keying = None

Body Related Features:

- ? Series = MCP
- ? Hybrid = No
- ? Number of Positions = 18
- ? Secondary Locking = Without

Housing Related Features:

- ? Housing Color = Black
- ? Housing Material = PBT - GF

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- ? Application = Used with Carrier Base P/Ns 1718484 and 1718485.

Other:

- ? Brand = AMP

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

