




1410191-3 Product Details


[Share](#)

[Print](#)


[Email](#)


1410191-3

TE Internal Number: 1410191-3



Active


[View 3D PDF](#)

MULTIGIG RT Connectors and Accessories


[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- Type of Connector = Daughtercard
- Industry Standard Configuration = VITA 46
- 20.3 mm Card Slot Pitch
- Module Type = Right

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)


[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [RIGHT-ANGLE PLUG ASSEMBLY, 7 ROW, RIGHT END, 20.3mm,...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [MULTIGIG RT* Signal Connectors, Tiers 1 and 2, and R...](#) (PDF, English)

Application Specifications:

- [MULTIGIG RT Signal Connectors](#) (PDF, English)

Instruction Sheets:

- [Removing MULTIGIG RT Right-Angle Module From Daughte...](#) (PDF, English)

CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version A)
- [3D Model](#) (IGES, Version A)
- [3D Model](#) (STEP, Version A)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Type of Connector = Daughtercard
- [Mount Angle](#) = Right Angle
- [Termination Type](#) = Single-Ended (SE)
- [Series](#) = None

Mechanical Attachment:

- [Module Type](#) = Right

Termination Features:

- Solder Tail Contact Plating = Tin-Lead over Nickel

Body Features:

- Card Slot Pitch (mm [in]) = 20.3 [0.8]
- Number of Columns = 16

Contact Features:

- Contact Base Material = Phosphor Bronze
- Contact Plating, Mating Area, Material = Gold

Housing Features:

- Housing Material = Liquid Crystal Polymer (LCP)
- Housing Color = Black
- UL Flammability Rating = UL 94V-0

Industry Standards:

- Industry Standard Configuration = VITA 46
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Tyco Electronics

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference Products](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

