Search Results

Evaluate
- FAQ's
Design a Solution
- Part Drawings
- PDF-Metered Powe ..
- Specification Sheets
- PDF-32 and 48 Am ..
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor
Install & Maintain
- Installation Instructions
- PDF-Panduit POU..

Home > Products Overview > Search Results >

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'VB1D2P3BN30P1'**

Your search criteria matched only one product, shown below

VB1D2P3BN30P1

Rack Mount Power Outlet Units
• Mounting brackets and screws included

Part Number	VB1D2P3BN30P1
RoHS Compliancy Status	Compliant
Part Description	Vertical power strip 32 Amp, 230/400V, WYE, twenty-four IEC G13, and six C-19 receptacles, three 16 A double pole magnetic breaker / on-off switch with integral switch guard, red LED current monitor, and 3 meter power cord with IEC 309 3P+N+ E pin in sleeve connector. Complies with IEC 60950– 1, EN 55022, EN 55024 and CE Marked. Dimensions: 66.3"H x 2.0"W x 2.0"D (1683mm x 51mm x 51mm)
Product Type	Vertical Power Outlet Unit
Color	Black
Depth (In.)	2.0
Depth (mm)	51
Height (In.)	66.3
Height (mm)	1683
Width (In.)	2.0
Width (mm)	51
CE Compliant	Yes
Plug Type	IEC 309 3P+N+ E
Pricing Description	Vertical, (24) C-13 & C-19, Metered 230,400V / 32A / Three-Phase POU
Min. Order UOM	PC
Min. Order Qty.	1
Voltage	230/400V
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP All rights reserved. | Legal Information | Privacy Policy