


## 1734261-5 Product Details

### Have a Question?

Chat with a Product Information Specialist



**1734261-5**

TE Internal Number: 1734261-5

Active

View 3D PDF

### High Performance Interconnects (HPI)

Always EU RoHS/ELV Compliant ([Statement of Compliance](#))

#### Product Highlights:

- Connector
- Preloaded
- Housing Gender = Header - Pin
- Contact Gender = Pin
- Housing Color = Natural

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Mating Products \(4\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [WIRE TO BOARD MALE HEADER, 1.25 MM PITCH, SMT, RIGHT...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- [Wire To Board serial, DIP, Pitch 1.25](#) (PDF, English)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version A)
- [3D Model](#) (IGES, Version A)
- [3D Model](#) (STEP, Version A)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)
- [Mating Products \(4\)](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Connector
- [Mount Angle](#) = Right Angle

#### Body Related Features:

- [Number of Positions](#) = 5
- [Centerline \(mm \[in\]\)](#) = 1.25 [0.049]
- [Number of Rows](#) = Single
- Locking Interface = Without
- Post Material = Phosphor Bronze
- Post Plating = Tin over Nickel

#### Contact Related Features:

- Preloaded = Yes
- Contact Gender = Pin
- [Contact Termination Type](#) = Surface Mount
- Contact Base Material = Phosphor Bronze
- Contact Finish = Tin over Nickel

#### Housing Related Features:

- [Housing Gender](#) = Header - Pin
- [Housing Color](#) = Natural
- UL Flammability Rating = UL 94V-0
- Housing Material = High Temperature Thermoplastic

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- Packaging Method = 24mm Tape & Reel
- Packaging Quantity = 1,000/Reel

#### Other:

- Brand = Tyco Electronics

BOOKMARK

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

Follow us on:

