

Catalog

- ▶ [Home](#)
- ▶ [Part Number Search](#)
- ▶ [Document Search](#)
- ▶ [CAD Model Search](#)
- ▶ [Text Search](#)
- ▶ [Alternate/Lead Free Part Search](#)
- ▶ [Multiple Part Comparison](#)
- ▶ [Alphabetical Search](#)
- ▶ [Brand Search](#)
- ▶ [Industry Product Search](#)
- ▶ [Product Type Search](#)
- ▶ [Product Family Search](#)
- ▶ [Competitor Cross Reference](#)
- ▶ [Lead Free Solutions](#)
- ▶ [Tool Search](#)
- ▶ [Help/Glossary](#)

Soft Shell Connectors

↳ .250" Centerline, 600 V, 19 - 36 A max. (Universal MATE-N-LOK)

AMP

926682-3



Active

 Directive 2002/95/EC
 Compliant

RoHS Compliant

(Tyco Electronics P/N:
926682-3)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ▶ General Info ▶ Sales Info ▶ Assembly Subcontractors 	<ul style="list-style-type: none"> ▶ Pricing ▶ Product Availability 	<ul style="list-style-type: none"> ▶ Tooling

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Not reviewed for lead free solder process
Product Type:	Housing
Connector Line:	Universal MATE-N-LOK
CompactPCI:	No
Centerline, Matrix (mm [in]):	6.35 x 6.35 [.250 x .250]
No. of Circuits:	6
Contact Layout:	Matrix
Housing Type:	Receptacle (Cap)
Mount:	Free Hanging
Housing Material:	Polyamide

Other Properties:

RoHS/ELV Compliance History:	Always was compliant
Contact Diameter (mm [in]):	2.13 [0.084]
Packaging Quantity:	100
Voltage (VAC):	600
Packaging Method:	One Piece Housing
Housing Flammability Rating:	UL 94V-0

Color:	Brick Red
Lock Type:	Positive Lock
High Current:	No
Sealable:	No
Current Rating (Amps.):	19

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)