



963142-1 Product Details

[Share](#) [Print](#) [Email](#)


963142-1

TE Internal Number: 963142-1

 Active

 [View 3D PDF](#)

Micro-Power & Power Quadlok System

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Accessory
- Accessory Type = Wire Seal
- Wire Range = 0.50-0.75² [20-18] mm [AWG]
- Cavity Diameter = 4.00 mm
- GET 0.64 Connector System

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Micro Quadlok System Tabellenzeichnung Buchsenkontakt \(PDF, German\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing \(DXF, Version A\)](#)
- [3D Model \(IGES, Version A\)](#)
- [3D Model \(STEP, Version A\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Accessory
- Accessory Type = Wire Seal
- Cable Type = FLR (Thin Walled Cable)
- Color = Black

Body Features:

- [Wire Range \(mm \[AWG\]\)](#) = 0.50-0.75² [20-18]
- [Cavity Diameter \(mm \[in\]\)](#) = 4.00 [0.157]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- [Accepts Wire Insulation Diameter, Range \(mm \[in\]\)](#) = 1.40 - 1.90 [0.055 - 0.075]

Other:

- [GET 0.64 Connector System](#) = Yes
- [Brand](#) = AMP

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

