



## 5447647-3 Product Details

### Have a Question?

Chat with a Product Information Specialist



**5447647-3**

TE Internal Number: 5447647-3

Active

### SMA/QMA RF Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Connector - RF
- RF Connector Type = SMA
- Plug
- Applies To Coaxial Cable
- Without Snap-Lock

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

### Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Connector - RF
- RF Connector Type = SMA
- [Gender](#) = Plug
- [Crimp Type](#) = Hex
- [Body Style](#) = Straight
- [Body Material](#) = Brass
- [Body Finish](#) = Nickel
- [Center Contact](#) = With
- [Retractable Collar](#) = Without
- [Safety Wire Holes](#) = Without

#### Mechanical Attachment:

- [Panel Attachment](#) = Without

#### Electrical Characteristics:

- Frequency = 12.4 GHz (Max.)

#### Termination Related Features:

- [Coaxial Cable Termination Type](#) = Crimp

#### Body Related Features:

- Snap-Lock = Without
- [Length \(mm \[in\]\)](#) = 24.90 [0.981]
- Center Contact Crimp Setting = 4

#### Configuration Related Features:

- [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 174, 188A, 316

#### Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- [Applies To](#) = Coaxial Cable

#### Other:

- Brand = AMP

BOOKMARK

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

Follow us on:

