


## 54792-1 Product Details


### Have a Question?

Chat with a Product Information Specialist



**54792-1**

TE Internal Number: 54792-1

 [Active](#)

### DIP Switches - Preprogrammed

 [5 of 6 EU RoHS/ELV Compliant](#) ([Find RoHS Compliant Alternates/Statement of Compliance](#))

#### Product Highlights:

- Switch - Mechanical
- Switch Style = Preprogrammed
- Switch Type = DIP
- 16 Positions
- Actuator Style = Screwdriver Slot

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Recommended PC Board Hole Pattern](#)
- [Pin Schematic](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Switch - Mechanical
- [Actuator Style](#) = Screwdriver Slot
- [Code Type](#) = Hexadecimal w/Complement
- [Stamping Legend](#) = I
- [Sealed Bottom](#) = With
- [Removable Tape Seal](#) = With
- Comment = All switches marked with epoxy ink unless otherwise noted.

#### Body Related Features:

- Switch Style = Preprogrammed
- Switch Type = DIP
- Number of Positions = 16

#### Contact Related Features:

- Contact Base Material = Copper Alloy
- Contact Plating, Mating Area, Material = Gold

#### Housing Related Features:

- Housing Material = Polyester GF
- UL Flammability Rating = UL 94V-0

#### Industry Standards:

- [RoHS/ELV Compliance](#) = ELV compliant, 5 of 6 Compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

#### Other:

- Brand = Alcoswitch

 [BOOKMARK](#) 

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)


### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address 

Follow us on:

