


770666-2 Product Details

Have a Question?

Chat with a Product Information Specialist



770666-2

TE Internal Number: 770666-2

 Active

 [View 3D PDF](#)

MTA, CST, CST-100 II and SL Contacts

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Contact Configuration = CST-100 Contacts
- Crimp Termination Method to Wire/Cable
- Gold Flash over Palladium Nickel or Gold (30) over Nickel Contact Plating, Mating Area, Material
- Wire Size = 0.12-0.4² [26-22] mm² [AWG]
- Used For CST-100 Housings

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [RECEPTACLE, CST-100, LOOSE PIECE \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [CONNECTOR, CRIMP-SNAP TERMINAL, .100 INCH CENTERLINE \(PDF, English\)](#)

Application Specifications:

- [CST-100 Connectors for Crimp Snap Terminals \(PDF, English\)](#)

Instruction Sheets:

- None Available

CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing \(DXF, Version H\)](#)
- [3D Model \(IGES, Version H\)](#)
- [3D Model \(STEP, Version H\)](#)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Product Photo](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Method to Wire/Cable](#) = Crimp
- [Wire Size \(mm² \[AWG\]\)](#) = 0.12-0.4² [26-22]
- [Used For](#) = CST-100 Housings
- Wire Insulation Diameter (mm [in]) = 1.65 [0.065]
- Dual Wipe Contact = Yes

Contact Related Features:

- Contact Configuration = CST-100 Contacts
- Contact Plating, Mating Area, Material = Gold Flash over Palladium Nickel or Gold (30) over Nickel
- Contact Base Material = Phosphor Bronze
- Contact Shape = Box

Industry Standards:



- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- [Packaging Method](#) = Loose Piece

Other:

- Brand = AMP

 [BOOKMARK](#) 

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

