


1612275-3 Product Details

[Share](#) [Print](#) [Email](#)


1612275-3

TE Internal Number: 1612275-3

 [Active](#)

0.025 Series and Hybrid Connectors and Contacts

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- Housing
- Connector Style = Plug
- Contact Type = Receptacle
- .64/2.3II Plug Configuration, 025/090 Plug Configuration

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [SEALED EFI ECU 0.64/2.3II I/O CONNECTOR 126POS/89POS...](#) (PDF, Japanese)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [SEALED EFI ECU 0.64/2.3II I/O CONNECTOR \(1\)](#) (PDF, Japanese)
- [SEALED EFI ECU 0.64/2.3II I/O CONNECTOR \(2\)](#) (PDF, Japanese)

Application Specifications:

- [CRIMPING OF SEALED 0.64 RECEPTACLE](#) (PDF, Japanese)

Instruction Sheets:

- [SEALED EFI ECU 0.64/2.3II I/O CONNECTOR \(1\)](#) (PDF, Japanese)
- [SEALED EFI ECU 0.64/2.3II I/O CONNECTOR \(2\)](#) (PDF, Japanese)

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Connector Type](#) = Housing
- [Plug Configuration](#) = .64/2.3II, 025/090
- [Mount](#) = Free Hanging
- [Sealed](#) = Yes

Body Features:

- [Number of Positions](#) = 126/89

Contact Features:

- [Contact Type](#) = Receptacle

Housing Features:

- [Connector Style](#) = Plug
- [Housing Material](#) = PBT - GF
- [Housing Color](#) = Black

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- [Applies To](#) = Wire/Cable

Packaging Features:

- [Packaging Method](#) = Paper Box, Tray

Other:

- [Brand](#) = AMP
- [Comment](#) = Housing for use with Clip.

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

