

1-1470364-2 Product Details

[Share](#) [Print](#) [Email](#)


1-1470364-2

TE Internal Number: 1-1470364-2

 Active

 [View 3D PDF](#)

High Performance Interconnects (HPI)

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- Housing
- Connector Style = Receptacle
- Contact Type = Socket
- Housing Color = White

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Mating Products \(3\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [1.0MM PITCH WIRE TO BOARD CONN., RCPT., SMT, HOUSING.](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Wire To Board Serial, SMT, Pitch 1.0](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version 0)
- [3D Model](#) (IGES, Version 0)
- [3D Model](#) (STEP, Version 0)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)
- [Mating Products \(3\)](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- Connector Type = Housing

Body Features:

- [Number of Positions](#) = 12
- [Centerline \(mm \[in\]\)](#) = 1.00 [0.039]
- [Number of Rows](#) = Single
- Locking Interface = Without

Contact Features:

- Contact Type = Socket

Housing Features:

- Connector Style = Receptacle
- [Housing Color](#) = White
- UL Flammability Rating = UL 94V-0
- Housing Material = Thermoplastic - GF

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = AMP

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

