


Terminals and Splices

POSITIVE LOCK Connectors (Mark II) / Commercial Type

187 Series (Straight-type)

Receptacle Housing



For 2 Circuits (6 mm Pitch)

Material : UL94V-2 rated,
66 Nylon

Part No. : 1-172210-1 (Natural)
172210-2 (Black)
172210-4 (Yellow)
172210-6 (Blue)

Material : UL94V-0 rated,
66 Nylon

Part No. : 1-172210-1 (Natural)
1-172210-2 (Black)
1-172210-4 (Yellow)
1-172210-5 (Green)
1-172210-6 (Blue)
1-172210-7 (Red)


For 2 Circuits (6 mm Pitch,
with Polarized Guide)

Material : UL94V-2 rated, 66 Nylon

Part No. : 1-174587-1 (Natural)
174587-4 (Yellow)

Material : UL94V-0 rated, 66 Nylon

Part No. : 1-174587-1 (Natural)
1-174587-4 (Yellow)
1-174587-5 (Green)
1-174587-6 (Blue)
1-174587-7 (Red)




For 2 Circuits (7 mm Pitch)

Material : UL94V-2 rated, 66 Nylon

Part No. : 1-175578-1 (Natural)
175578-2 (Black)
175578-4 (Yellow)
175578-6 (Blue)

Material : UL94V-2 rated, 66 Nylon


Part No. : 1-175578-1 (Natural)
1-175578-2 (Black)
1-175578-4 (Yellow)
1-175578-5 (Green)
1-175578-6 (Blue)
1-175578-7 (Red)



For 2 Circuits (10 mm Pitch)

Material : UL94V-0 rated,
66 Nylon


Part No. : 1-179720-1 (Natural)
179720-2 (Black)
179720-4 (Yellow)



For 2 Circuits (15 mm Pitch,
for electro-magnetic)

Material : UL94V-0 rated, 66 Nylon

Part No. : 1-176498-1 (Natural)
176498-2 (Black)
176498-4 (Yellow)
176498-6 (Blue)




For 2 Circuits(for Micro-Switch)

Material : UL94V-2 rated,
66 Nylon

Part No. : 1-174712-1 (Natural)
174712-6 (Blue)

Material : UL94V-0 rated,
66 Nylon

Part No. : 1-174712-1 (Natural)
1-174712-4 (Yellow)
1-174712-6 (Blue)
1-174712-7 (Red)




For 3 Circuits (for Micro-Switch)

Material : UL94V-2 rated,
66 Nylon

Part No. : 1-172075-1 (Natural)
172075-4 (Yellow)
172075-6 (Blue)

Material : UL94V-0 rated,
66 Nylon


Part No. : 1-172075-1 (Natural)
1-172075-4 (Yellow)



For 4 Circuits (for Timer)

Material : UL94V-0 rated,
66 Nylon

Part No. : 1-174513 (Natural)



For 4 Circuits (for Power Relay)

Material : UL94V-2 rated,
66 Nylon

Part No. : 1-173150-1 (Natural)
173150-4 (Yellow)

Material : UL94V-0 rated,
66 Nylon

Part No. : 1-173150-1 (Natural)
1-173150-4 (Yellow)

