



Have a Question?
 Chat with a Product Information Specialist


Japan Update

What can we help you find?



1-1718333-1 Product Details

Share |
 Print |
 Email



1-1718333-1

TE Internal Number: 1-1718333-1



Active



View 3D PDF

Micro-Power & Power Quadlok System

[Always EU RoHS/ELV Compliant](#) (Statement of Compliance)

Product Highlights:

- Connector
- Housing
- Connector Style = Receptacle
- Contact Type = Receptacle
- 2 Positions

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> • 2D Drawing (DXF, Version A) • 3D Model (IGES, Version A) • 3D Model (STEP, Version A) 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Connector • Connector Type = Housing • Sealed = No • Keyed = Yes <p>Body Related Features:</p> <ul style="list-style-type: none"> • Number of Positions = 2 • Wire Range (mm [AWG]) = 0.20-0.75² [24-18] • Centerline Matrix (mm [in]) = 2.54 [.100] • Staggered Centerline = Without • Key ID = A <p>Contact Related Features:</p> <ul style="list-style-type: none"> • Contact Type = Receptacle • Contact Style = MQS 	<p>Housing Related Features:</p> <ul style="list-style-type: none"> • Connector Style = Receptacle • Housing Color = Black • Housing Material = PBT - GF <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • Retainer = With • RoHS/ELV Compliance History = Always was RoHS compliant <p>Purchasing Information:</p> <ul style="list-style-type: none"> • Retainer Color = Black <p>Other:</p> <ul style="list-style-type: none"> • GET 0.64 Connector System = No • Brand = AMP

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:

Visit Us On:



[Provide Website Feedback](#)

