Standard Extraction Tool

Insert discrete terminals into connector housings or remove them, without causing damage to either the terminals or housings.

Image representative of type only

Features:

This standard tool design features a comfortable handle and snapin/out protective cover. Users can stow the business end of the tool when not in use, to protect against inadvertent damage to product or personal injury.



Revised:

Part Number	Description	mm ² (AWG) or other
1-1579007-1	AMP MCP 1.5k; AMP MCP 1.5k (SWS)	
1579007-1	AMP MCP 2.8	
1-1579007-3	AMP MCP 6.3/4.8k Receptacle	
1-1579007-7	AMP MCP 9.5 Tab; Maxi Power TIMER Receptacle	
1-1579008-6	AMP-DUAC Connectors	
1579007-9	AMPLIMITE HD-20	
1-1579007-5	ECONOSEAL III LC 1.8 [.070]	
3-1579007-6	GET .064 Pin/Socket	
1579008-5	IEC-Terminal	
4-1579007-1	Locking Tab 3.3 Receptacle	
539764-1	MATE-N-LOK 3.5 (.140)	
1-1579007-0	MCON 1.2-CB Receptacle; MCON 1.2-CB Receptacle (SWS) - Secondary Lock	
1579007-8	MCON 1.2-CB; MCON 1.2-CB (SWS)	
5-1579007-3	MCON 1.2-LL; MCON 1.2-LL (SWS)	
5-1579008-2	MCON 2.8 Receptacle; MCON 2.8 Receptacle (SWS)	
6-1579007-3	Micro Power Quadlok	
5-1579007-5	Micro TIMER I	
539960-1	Micro TIMER II, III, IV; TAB 1.6	
4-1579007-8	MQS	
6-1579007-0	MQS Clean Body	
3-1579007-7	Pin Ø1.5 (Spare tube 3-1579007-8)	
1-1579007-8	Pin/Socket Ø2.5 (Spare tube 4-1579007-7)	
539967-1	Pin/Socket Ø4.0 (Spare tube 5-1579007-2)	
6-1579007-4	Power Quadlok	
1579007-2	RAIL Contact	
7-1579007-0	SENSOR-TAB 1.5; SENSOR-REC 1.5 Type II	
2-1579007-5	Standard & Junior Power TIMER (asymmetric Tab contacts)	
1-1579007-6	Standard & Junior Power TIMER Receptacle and (symmetric Tab contacts)	
1-1579007-4	Standard & Junior TIMER; FASTIN-FASTON & POSITIVE-LOK Tab 2.8, 4.8, 5.8, 6.3	3
4-1579007-3	Standard TIMER etc. Kit comprises; 1-1579007-4 & 1-1579007-6	
9-1579007-1	SUPER-SEAL 1.5; MULTILOCK 070	
9-1579007-5	Universal MATE-N-LOK Contacts - only with Housing contact cavity Ø 3.55mm	
9-1579007-6	Universal MATE-N-LOK Socket 926884 / 926885 with Housing contact cavity Ø5.0	
539972-1	Universal MATE-N-LOK; Socket Ø1.5; TYPE II, III+; CI-2, -3, -H; Econoseal E Series (Spare tube 5-1579007-0)	

Extraction Tool

Insert discrete terminals into connector housings or remove them, without causing damage to either the terminals or housings.

Image representative of type only

Features:

Many different design types currently exist for our vast terminal range, which we continue to convert. If you would like the tool you use converted to our Standard design, want a custom kit or tools in this design for other manufacturers products please contact us, and where volumes permit we will be pleased to provide you with a quotation for your requirement.



Part Number	Description	mm² (AWG) or other
455822-1	AMP COMBO LINE	,
723986-1	AMP DRAWER	
234168-1	AMP DYNAMIC D-3	
409158-1	AMP DYNAMIC D-5	
465195-1	AMP-LEAF	
843473-1	AMP MOD I, IV, V; TANDEM SPRING	
166645-1	AMP MOD IV, V	
843477-1	AMP MOD MTE; SHORT-POINT	
913923-1	AMP UNIVERSAL Power Connector	
188688-1	AMP DUAC	
91285-1	AMPLIMITE HD-20	
726364-2	AMPLIMITE HD-22	
318813-1	AMPLIMITE size 8; POWERBAND .125	
318837-1	COMM 093	
465644-1	Commercial MATE-N-LOK	
1276716-1	DYNAMIC D2	
724712-1	ECONOSEAL III HC 6.3 [.250] Receptacle	
1102855-1	HTS HDM Contacts	
1102855-7	HTS HE/HA Contacts	
1102855-2	HTS HND Contacts	
1102855-8	HTS HSK Contacts	
1102855-4	HTS HSM Contacts	
1102855-5	HTS HSS Contacts	
1102855-3	HTS HVT Contacts	
91084-1	LOCKING CLIP	
753787-1	MIC MK-2 Receptacle B TYPE	
724763-1	MIC Mk-I Tab	
723735-1	MIC Mk-I&II	
843996-6	MICRO MATE-N-LOK	
189727-1	Mini-Universal MATE-N-LOK	
455822-2	MR Contacts	
1276565-1	MULTILOCK 025	
755430-1	MULTILOCK 040	
715131-1	MULTILOCK 040 MkII	
755430-2	MULTILOCK 070	
342578-1	PM IV Cable seal- dissassembly tool	
342576-1	PM IV Socket Ø3.0 mm	
724659-1	POSITIVE LOCK 4.8 [.187] Mk II Receptacle	
724659-2	POSITIVE LOCK 6.3 [.250] Mk II Receptacle	
724659-5	POSITIVE LOCK Mk II	
785084-1	SUPER-SEAL 1.5 (secondary lock of TAB Connector)	
69357-3	TERMI-POINT	0.08 - 0.6 [28-20]
91073-1	TWIN-LEAF	- · ·
305183-8	TYPE I; Miniature COAXICON	
726423	TYPE XII	

Standard Insertion Tool

Insert discrete terminals into connector housings or remove them, without causing damage to either the terminals or housings.

Image representative of type only

Features:

This standard tool design features a comfortable handle and snapin/out protective cover. Users can stow the business end of the tool when not in use, to protect against inadvertent damage or personal injury.



Part Number	Description	mm² (AWG) or other
1579008-9	AMP MCP 1.5 & 2.8 and Housings; 284848 & 284844	
5-1579018-6	Tab 1.6 (SWS)	
3-1579007-2	Pin Ø2.5 (SWS) and Housing 1-967402-1	
1-1579007-9	Pin/Socket Ø4.0 (spare tube 5-1579007-1)	

Insertion Tool

Insert discrete terminals into connector housings or remove them, without causing damage to either the terminals or housings.

Image representative of type only

Features:

Many different design types currently exist for our vast terminal range, which we continue to convert. If you would like the tool you use converted to our Standard design, want a custom kit or tools in this design for other manufacturers products – contact us, and where volumes permit we will be pleased to provide you with a quotation for your requirement.



Part Number	Description	mm² (AWG) or other
380306-3	AMP 53 Series TAPER PIN	
552714-3	AMP Barrel Terminals	0.08 - 0.2 [28-24]
552714-4	AMP Barrel Terminals	0.08 - 0.4 [28-22]
552714-1	AMP Barrel Terminals	0.4 - 1.0 [22-18]
58430-1	AMPLIMITE .050 Shielded Connectors	
726363-2	AMPLIMITE HD-22	
344525-1	ECONOSEAL III, High Current with Seal	0.5 - 3.0 [20-14]
465665-1	FASTIN-FASTON 6.3 [.250] - requires Universal Handle 465629-1	
1102855-6	HTS Contacts	
274250-2	MAG-MATE	
59839-1	MTA-156	
965702-1	Pin/Socket Ø1.5 & Ø2.5 (Insulation less than Ø2.1mm)	Insulation less than Ø2.1mm
965700-1	Pin/Socket Ø4.0	
342577-1	PM IV Cable seal - assembly tool	
658167-1	RV-100	
725830-1	Standard TERMI-POINT	
658033-1	TYPE F	
200893-2	TYPE II, III+	
826790-3	TYPE III+, CI-2 Socket - Cable Seal protection tool	
826791-1	TYPE III+, CI-2 Pin - Seal protection tool	
455830-1	Universal MATE-N-LOK; Commercial MATE-N-LOK; Mini-Universal MATE-N-LOK	
1583255-1	Z-Pack HM-Zd Vertical Pin Header	

Tee Handled Insertion Tool

Features:

Comfortable moulded handle Moulded-in metal insert for long life Image representative of type only



Revised:

Part Number	Description	mm² (AWG) or other
229384-1	AMP CHAMP Connectors	
91287-1	AMPLIMITE HDE-20	
525421-5	HE-13; HE-14	0.08 - 0.22 [28-24]
1-525421-3	IDC Bulb Holder 5 mm	0.2 [24]
525421-6	IDC FASTON	0.2 - 0.4 [24-22]
59803-1	MTA 100	0.08 - 0.4 [28-22]
59804-1	MTA 156	0.15 - 1.0 [26-18]

Insertion / Extraction Tool Kit

Custom kits made to suit your specific requirements

Image representative of type only

Insert discrete terminals into connector housings or remove them, without causing damage to either the terminals or housings

Features:

Kits are supplied in a rugged plastic carry case

This standard tool design features a comfortable handle and snapin/out protective cover. Users can stow the business end of the tool when not in use, to protect against inadvertent damage or personal injury.



Part Number	Description	mm² (AWG) or other
/ ₋ 1570010 ₋ 0	Insertion / Extraction Tool Kit - Penault	