

1-2112162-1 Product Details

Share | Print | Email



1-2112162-1

TE Internal Number: 1-2112162-1

Active

[View 3D PDF](#)

Multiple Contact Point (MCP) & MCON Contact Systems

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Applies To Wire/Cable
- Wire/Cable Type = FLR (Thin Walled Cable)
- Connector
- Housing
- Connector Style = Plug

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version B)
- [3D Model](#) (IGES, Version B)
- [3D Model](#) (STEP, Version B)

[List all Documents](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Wire/Cable Type](#) = FLR (Thin Walled Cable)
- Product Type = Connector
- Connector Type = Housing
- Series = Multiple Contact Point (MCP)
- Mating Area Interface Dimensions (mm [in]) = 2.79 [.110]
- Sealed = Yes
- Mount Angle = Straight

Mechanical Attachment:

- Keying = A

Termination Features:

- Key Type = Standard

Body Features:

- Hybrid = No
- Number of Positions = 21
- Secondary Locking = With

Contact Features:

- Contact Type = Tab

Housing Features:

- Connector Style = Plug
- Housing Color = Black
- Housing Material = PBT - GF

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Applies To = Wire/Cable

Packaging Features:

- Packaging Method = Box

Other:

- Brand = Tyco Electronics

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

