


1445692 - 4 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



1445692 - 4

✓ [Active](#)

ARINC 600/404 Contacts and Accessories

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- ? Contact
- ? Pin
- ? Cable Type = Tensolite NF24Q100
- ? Terminate To Cable
- ? Gold over Nickel Contact Mating Area Plating Material

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [ASSEMBLY, PIN, QUADRAX, 2mm SQ, AIRCRAFT DATA NET...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? [Quadrax Circular Connectors and Quadrax Contacts](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version H)
- ? [3D Model](#) (IGES, Version H)
- ? [3D Model](#) (STEP, Version H)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Contact
- ? [Pin/Socket](#) = Pin
- ? Color Code = None
- ? [Connector Family](#) = ARINC 404, ARINC 600
- ? Body Style = Straight
- ? Crimp Type = Hex

Electrical Characteristics:

- ? Connector Impedance (?) = 100

Body Related Features:

- ? [Length \(mm \[in\]\)](#) = 31.37 [1.235]
- ? Solder Dipped = No
- ? Removal Style = Rear Release/Rear Remove
- ? Wire Seal Boot = With

Contact Related Features:

- ? [Contact Mating Area Plating Material](#) = Gold over Nickel
- ? [Contact Size](#) = 8
- ? Contact Type = Quadrax

Configuration Related Features:

- ? [Cable Type](#) = Tensolite NF24Q100

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- ? [Terminate To](#) = Cable

Other:

- ? Brand = AMP