



1825095-1 Product Details

[Share](#) | [Print](#) | [Email](#)


✔ **Active**

Pushbutton Switches

TP11CGPC004

1825095-1 ✔

TE Internal Number: 1825095-1

Product Highlights [View All](#)

- Switch
- Tactile
- Single Pole - Single Throw Configuration (Pole-Throw)
- Contact Rating = 0.4VA
- Process Sealed

- [Pricing & Availability](#) >
- [Request Sample](#) >
- [Add to My Part List](#) +
- [Buy Product through Distributor](#) >

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Switch
Mount Angle	Vertical
Actuator Style	Rectangular

Electrical Characteristics

Contact Rating	0.4VA
----------------	-------

Termination Features

Termination Type	Printed Circuit
------------------	-----------------

Body Features

Mount Style	Through-Hole
Actuator Profile	Flush
Actuator Color	Black
Case Material	Thermoplastic (LCP)
Actuator Material	Nylon

Contact Features

Contact Plating	Gold
Contact Base Material	Copper Alloy

Housing Features

Process Sealed	Yes
Low Profile	No

Configuration Features

Tactile	Yes
Configuration (Pole-Throw)	Single Pole - Single Throw
Operating Function	Off [On]
Ganged	No
ESD Grounding Terminal	Without
Number of Actuators	Single
Illuminated	No
Dust Proof	No
Support Bracket	Without
Snap Action	Without

Industry Standards

RoHS/ELV Compliance ?	RoHS compliant, ELV compliant
Lead Free Solder Processes ?	Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Temperature Rating	Standard
--------------------	----------

Operation/Application

Actuator Force (g [oz])	50.00 - 400.00 [1.770 - 14.120]
-------------------------	---------------------------------

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Other

Series ?	TP
Brand	Alcoswitch

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

