


## 160668-2 Product Details

 [Live Product Chat](#)




### 160668-2

TE Part Number: 160668-2

 [Active](#)

 [Add to Part List](#)

### Multiple Circuit Housings with Tabs & Receptacles Including FASTIN-FASTON

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Receptacle
- Tab Fit = 2.79 x 0.79 mm
- Wire Range = 0.50-1.50<sup>2</sup> [20-15.5] mm [AWG]
- Insulation Diameter = 2.00-3.10 [.079-.122] mm [in]
- Receptacle Style = Straight

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Receptacle
- [Tab Fit \(mm \[in\]\)](#) = 2.79 x 0.79 [.110 x .031]
- [Insulation Diameter \(mm \[in\]\)](#) = 2.00-3.10 [.079-.122]
- [Receptacle Style](#) = Straight
- [Wire/Cable Type](#) = Regular Wire
- [Finish](#) = Pre-Tin
- [Material](#) = Brass
- [Insertion Force](#) = Normal
- [Insulation Support](#) = With
- [Crimp Type](#) = F-Crimp
- FASTON = Yes
- For Housing Type = Single or Multiple
- Comment = According to DIN 46340, Part 1

#### Body Related Features:

- [Wire Range \(mm \[AWG\]\)](#) = 0.50-1.50<sup>2</sup> [20-15.5]
- Stock Thickness (mm [in]) = 0.25 [0.010]

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- [Packaging Method](#) = Loose Piece

#### Other:

- Line = FASTIN-FASTON .110
- Brand = AMP

 [Provide Website Feedback](#) | [Need Help?](#)