

221117-4 Product Details

[Live Product Chat](#)



221117-4

TE Part Number: 221117-4

[Active](#)

[Add to Part List](#)

SMA/QMA RF Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- Plug
- Connector Type = SMA
- Without Snap-Lock
- Terminate To Coaxial Cable

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [PLUG ASSEMBLY SERIES SMA \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Gender](#) = Plug
- [Connector Type](#) = SMA
- [Crimp Type](#) = Dual
- [Body Style](#) = Straight
- [Body Material](#) = Brass
- [Body Finish](#) = Nickel
- [Center Contact](#) = With
- [Retractable Collar](#) = Without
- [Safety Wire Holes](#) = Without
- Dielectric Material = TEFLON
- Coupling Nut Material = Brass
- Coupling Nut Finish = Nickel
- Gasket Material = Silicone Rubber

Mechanical Attachment:

- [Panel Attachment](#) = Without

Termination Related Features:

- [Coaxial Cable Termination Type](#) = Crimp

Body Related Features:

- Snap-Lock = Without
- [Length \(mm \[in\]\)](#) = 30.18 [1.188]
- Ferrule Material = Copper

Contact Related Features:

- Center Contact Material = Brass
- Center Contact Plating = Gold

Configuration Related Features:

- [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 174, 188, 188A, 316

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Terminate To](#) = Coaxial Cable

Other:

- Brand = AMP

[Provide Website Feedback](#) | [Need Help?](#)