


## 2-5330830 -4 Product Details

**Live Product Chat** US Only  
 8:30am - 5pm ET, Mon - Fri



**2-5330830 -4**

[Active](#)

### UHF/ Miniature UHF, RF Connectors

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Connector
- ? Plug
- ? Terminate To Coaxial Cable
- ? Without Snap -Lock
- ? Coaxial Cable Termination Type = Crimp

[View all Features](#) | 
 [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- ? [COAXICON CONNECTOR UHF PLUG](#) (PDF, English)

##### Catalog Pages/Data Sheets:

- ? None Available

##### Product Specifications:

- ? None Available

##### Application Specifications:

- ? None Available

##### Instruction Sheets:

- ? None Available

##### CAD Files:

- ? None Available

##### Additional Information:

- ? [Product Line Information](#)

##### Additional Product Images:

- ? [Recommended Panel Cutout](#)

##### Related Products:

- ? [Tooling](#)

[List all Documents](#)

#### Product Features

(Please use the Product Drawing for all design activity)

##### Product Type Features:

- ? [Product Type](#) = Connector
- ? [Gender](#) = Plug
- ? [Body Size](#) = Standard
- ? [Crimp Type](#) = Dual
- ? [Dielectric Material](#) = Polypropylene
- ? Rubber Gasket = Without
- ? Panel Thickness (mm [in]) = 2.54 [0.100]

##### Mechanical Attachment:

- ? [Panel Attachment](#) = With
- ? [Panel Attachment Method](#) = Bulkhead

##### Termination Related Features:

- ? [Coaxial Cable Termination Type](#) = Crimp

##### Body Related Features:

- ? Snap -Lock = Without
- ? [Body Plating](#) = Nickel

##### Contact Related Features:

- ? [Center Contact Plating](#) = Silver

##### Configuration Related Features:

- ? [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 58

##### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

##### Conditions for Usage:

- ? [Terminate To](#) = Coaxial Cable

##### Packaging Related Features:

- ? [Packaging Method](#) = Strip

##### Other:

- ? Brand = AMP