


293041-1 Product Details

[Share](#) |
 [Print](#) |
 [Email](#)



293041-1

TE Internal Number: 293041-1

Active

[View 3D PDF](#)

Multiple Circuit Housings with Tabs & Receptacles

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Contact
- Contact Type = Tab
- Mating Area Interface Dimensions = 6.35 x 0.80 mm
- Wire Range = 0.35-1.00² [28-17] mm [AWG]
- Insulation Diameter = 2.03 [.080] Max. mm [in]

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [FASTIN-FASTON Connector, 6.3 mm SR. TAB CONTACT \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [FASTIN-FASTON CONN. .110 INCH, .187 INCH, .250 INCH,... \(PDF, English\)](#)

Application Specifications:

- [FASTIN-FASTON* Connectors, 6.3 mm series TAB CONTACT. \(PDF, Italian\)](#)

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version B1\)](#)
- [3D Model \(IGES, Version B1\)](#)
- [3D Model \(STEP, Version B1\)](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Contact
- Wire/Cable Type = Regular Wire
- Finish = None
- Insertion Force = Normal
- Insulation Support = With
- FASTON = Yes

Termination Features:

- Crimp Type = F-Crimp

Dimensions:

- Mating Area Interface Dimensions (mm [in]) = 6.35 x 0.80 [.250 x .031]
- Insulation Diameter (mm [in]) = 2.03 [.080] Max.

Body Features:

- Wire Range (mm [AWG]) = 0.35-1.00² [28-17]
- Material = Brass

Contact Features:

- Contact Type = Tab

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Packaging Features:

- Packaging Method = Reel
- Packaging Quantity = 3,000/Reel

Other:

- Line = FASTIN-FASTON .250
- Brand = TE Connectivity
- Comment = With hole

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

