




1996705-4 Product Details


[Share](#)

[Print](#)

[Email](#)


1996705-4

TE Internal Number: 1996705-4



Active


[View 3D PDF](#)

SMP/SMPP RF Connectors


[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Module
- RF Connector Type = SMPP
- Mount = Printed Circuit Board
- Right Angle Mount Angle
- Mounting Hole Diameter = 2.54 mm

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)


[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [8 POSITION R.F. MODULE, P.C.B. MOUNT VITA 67 DAUGHTER...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Modular, High Density, RF Connection System](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- [Vita 67.1 and 67.2 R.F. Module Mounting Patterns](#) (PDF, English)

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version K)
- [3D Model](#) (IGES, Version K)
- [3D Model](#) (STEP, Version K)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Module
- RF Connector Type = SMPP
- Mount = Printed Circuit Board
- Mount Angle = Right Angle
- Mounting Hole Diameter (mm [in]) = 2.54 [0.1]
- Termination Type = Screw

Body Features:

- Center-to-Center Spacing (mm [in]) = 6.1 [0.24]
- Number of Positions = 8

Contact Features:

- Plating Material = Passivated

Housing Features:

- Housing Material = Stainless Steel

Industry Standards:

- VITA 67 = Yes
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = AMP

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

