


53880-2 Product Details

[Live Product Chat](#)



53880-2

TE Part Number: 53880-2

[Active](#)

[Add to Part List](#)

[View 3D PDF](#)

Power Lock Connectors

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Contact
- Wire Range = 5.00-15.00² [10-6] mm [AWG]
- Product Series = Series II
- Wire Termination Type = Crimp
- Strip

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [CONTACT, SERIES 2, POWER LOCK](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [PRODUCT SPECIFICATION CONNECTOR, POWER LOCK, SERIES 2](#) (PDF, English)

Application Specifications:

- [Power Lock Series 75 Connectors](#) (PDF, English)
- [Power-Lock 75 Series Contacts](#) (PDF, Japanese)

Instruction Sheets:

- [Power Lock Connectors \(Series II\) \(Accept Contacts 5...](#) (PDF, English)
- [Inspection of Series II Power Lock Contacts](#) (PDF, English)

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version M)
- [3D Model](#) (IGES, Version M)
- [3D Model](#) (STEP, Version M)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Contact
- Product Series = Series II
- Wire Termination Type = Crimp

Body Related Features:

- [Wire Range \(mm \[AWG\]\)](#) = 5.00-15.00² [10-6]
- Stock Thickness (mm [in]) = 1.22 [0.048]

Contact Related Features:

- Contact Material = Copper
- Contact Mating Area Plating Material = Silver

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- [Packaging Method](#) = Strip

Other:

- Brand = AMP

[Provide Website Feedback](#) | [Need Help?](#)