



5-1634503-3 Product Details

Share Print Email



Active

View 3D PDF

BNC RF Connectors

BNC Str PCB Skt 75Ohm Nickel Pltd

5-1634503-3

TE Internal Number: 5-1634503-3

Product Highlights View All

- Connector - RF
- Jack
- Connector Style = Jack
- Applies To Printed Circuit Board
- PCB Mounting Orientation = Vertical

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through
Distributor

Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Connector - RF
Gender	Jack
PCB Mounting Orientation	Vertical
Grade	Commercial
PCB Mount Retention	With
PCB Mount Retention Type	Hold Down Post(s)
Mounting Post Style	Round
Sealed	No
Isolated	No
Dielectric Material	Polymethylpentene

Mechanical Attachment

Surface Mountable	No
Hardware Included	No
Panel Mount Retention	Without

Electrical Characteristics

Connector Impedance (Ω)	75
-------------------------	----

Dimensions

PCB Height (mm [in])	13.70 [0.539]
Mounting Post Length (mm [in])	4.50 [0.177]
PCB Thickness, Recommended (mm [in])	3.20 [0.126]

Body Features

Body Shape	Circular
Body Material	Zinc
Body Plating	Nickel
Body Insulation	Without
Polarized	No
Mount Direction	Front

Contact Features

Center Contact Material	Phosphor Bronze
Center Contact Plating	Gold

Housing Features

Connector Style	Jack
-----------------	------

Configuration Features

Number of Ports	1
-----------------	---

Industry Standards

Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Always was RoHS compliant

Environmental

Operating Temperature (Max.) (°C)	85
-----------------------------------	----

Conditions for Usage

Applies To	Printed Circuit Board
For Use With	ZDC/BNC Connector

Packaging Features

Packaging Method	Individual
------------------	------------

Other

Brand	Greenpar
Comment	Low Profile.

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

Corporate Information

About TE
Investors
News Room
Supplier Portal
Careers
Terms & Conditions
Privacy Policy
Global Accessibility Statement

Quick Links

Distributor Inventory
Product Cross Reference
Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat With Us
Find a Phone Number
Knowledge Base
Manage Your Account

Keep Me Informed

