


## 5-555179-3 Product Details



5-555179-3

### Modular Plugs and Accessories

Not reviewed for RoHS Compliance

#### Product Highlights:

- Connector
- Performance Category = Cat 3
- 8 Contacts Loaded
- Shielded
- Connector Style = Plug - Modular

[View all Features](#)

#### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 5-555179-3

Superseded

[Search for Replacement Parts](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [MODULAR PLUG ASSEMBLY 8 POSITION,SHIELDED, ROUND CABLE \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Connector
- Performance Category = Cat 3
- Cable Style = Round Stranded
- Latch Style = Standard
- Keyed = No
- Small Conductor = No

#### Electrical Characteristics:

- Shielded = Yes

#### Termination Features:

- Solder Tail Contact Plating = Gold Flash over Nickel

#### Dimensions:

- Conductor Outer Diameter (mm [in]) = 0.74 - 0.99 [0.029 - 0.039]

#### Contact Features:

- Contact Base Material = Phosphor Bronze
- Contact Plating, Mating Area, Material = Gold (50)

#### Housing Features:

- Connector Style = Plug - Modular
- Housing Material = Polycarbonate GF
- UL Flammability Rating = UL 94V-2

#### Configuration Features:

- Number of Contacts Loaded = 8
- Number of Positions = 8

#### Industry Standards:

- RoHS/ELV Compliance = Not reviewed for ELV/RoHS compliance
- Lead Free Solder Processes = Not reviewed for lead free solder process

#### Packaging Features:

- Packaging Method = Box
- Qty./Box = 100
- Boxes/Carton = 10

#### Product Availability:

- Region = Not Specified

#### Other:

- Brand = AMP

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed

