

8080-1G2-LF Product Details

[Share](#) |
 [Print](#) |
 [Email](#)



8080-1G2-LF
(6-1437504-4)

TE Internal Number: 6-1437504-4

[Active](#)

Transistor Sockets and Adapters

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Socket
- Terminal Style = Solder
- Terminal Configuration = Contact
- Lead Size Accepted = 1.02 mm
- 3 Terminals

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [TRANSISTOR SOCKET](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Socket
- Terminal Configuration = Contact
- Product Series = 8080-1G Series
- Package = TO-3

Electrical Characteristics:

- Number of Solder Lugs = 2

Termination Features:

- Terminal Plating = Silver

Body Features:

- Terminal Style = Solder
- Number of Terminals = 3
- Socket Type = Transistor
- Terminal Material = Beryllium Copper
- Insulator Material = Diallyl Phthalate

Configuration Features:

- Lead Size Accepted (mm [in]) = 1.02 [0.040]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Operating Temperature (°C) = -55 - +125

Other:

- Brand = AMP

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

