
Double-Pole Round Rocker Switch





Features

- Single Pole and Double pole configurations
- Lighted and non-lighted options
- Industry standard cutout
- Mechanical life: min. 100,000 operations

Electrical Ratings

	EN61058 Rating		Electrical Life at Rated Load					
Switch Series		UL1054 Rating	According to VDE (Min. Operations)	According to UL (Min. Operations)				
RR	10(4)A, 250V~ T125/55 10A 125VAC 1/4HP 8A 250VAC 1/4HP		10,000	6,000				

Electrical Specifications		Material Specificati	Material Specifications		
	10A, 125VAC 1/4HP 8A 250VAC 1/4HP; (cULus) 10(4)A, 250V~ T125/55 (VDE)	Actuator:	Nylon 66 94V-2		
Ratings:		Base:	Nylon 66 94V-2		
Dielectric Strength:	1000VAC for 1 minute	Spring:	Steel Wire		
Insulation Resistance:	100M ohms min at 500VDC	Contacts:	Silver Alloy		
Initial Contact Resistance:	0.020 ohms max	Movable Arm:	Copper Alloy		
Temperature Range:	-20°C to + 65°C	Terminals:	Tin-Plated Copper Alloy		

RoHS Compliant UL File No: E23301

Specifications subject to change without notice.










Single-Pole Rocker Switch

Dimensions inches






Recommended Panel Cut-Out Dimensions Inches(mm) 0.039 to 0.078 (1.0 to 2.0)



Ordering Information



Examples of Common Part Numbers and Descriptions inches (mm)

Part Number RRA22H3BBBNN		Switch Function On – Off	Terminal Type 0.187 (4.8) Quick-Connect	Actuator/ Housing Color Black/ Black	Legend Marking	Contact	
RRA32H3FBBNN	-0-0-	On – Off	0.187 (4.8) Quick-Connect	Black/ Black		Call, fax or visit our Website for more information.	The manufacturer accepts no n. liability for errors or non-availability,
RRA22H3BWWNN	<u> </u>	On – Off	0.187 (4.8) Quick-Connect	White/ White	\bigcirc	ZF Electronics Corporation and reserves a specifications 11200 88th Avenue	and reserves the right to change specifications without prior notice.
RRA22H3FBRNN	<u> </u>	On – Off	0.187 (4.8) Quick-Connect	Red/ Black		Pleasant Prairie, WI 53158 Phone: 262.942.6500 Web: www.cherrycorp.com	Technical data relates to product specifications only. Features may differ from those described. Only
RRA22H3BBRLN	2001 	On – Off/Lighted	0.187 (4.8) Quick-Connect	Red/ Black	\bigcirc	Email: <u>cep_sales@zf.com</u> Fax: 262.942.6566	drawings combined with product specifications shall be deemed binding.
RRA32H3BBRLN		On – Off/Lighted	0.187 (4.8) Quick-Connect	Red/ Black	\bigcirc		© 2007 ZF Electronics Corporation
							Last Updated: 10/01/12

