


## FCB - 205 - 0226M Product Details

[Share](#)
[Print](#)
[Email](#)



**FCB - 205 - 0226M**  
 (5 - 1617758 - 2)

TE Internal Number: 5 - 1617758 - 2

 [Active](#)

### Military/Aerospace Mid - Range Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- ? FCB 5 - 10 Amp Relay Series
- ? DC Actuating System
- ? Coil - Rated Voltage = 28 VDC
- ? Contact Arrangement = 2 Form C, DPDT, 2 C/O
- ? Current Rating = 5 A

[View all Features](#)

#### Quick Links

- ? [Check Pricing & Availability](#)
- ? [Search for Tooling](#)
- ? [Product Feature Selector](#)
- ? [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [MSD\\_RELAY](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? Series = FCB 5 - 10 Amp Relay
- ? [Terminal Configuration](#) = Solder Hook

#### Electrical Characteristics:

- ? [Actuating System](#) = DC
- ? [Coil - Rated Voltage \(VDC\)](#) = 28
- ? [Current Rating \(A\)](#) = 5

#### Termination Features:

- ? [Terminal Plating](#) = Tin -Lead
- ? Auxiliary Contacts = Without

#### Body Features:

- ? [Mount Type](#) = Side Mount

#### Configuration Features:

- ? [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- ? [Coil Suppression Diode](#) = With
- ? Coil - Magnetic System = Polarized, Monostable

#### Industry Standards:

- ? Government/Industry Qualification = Yes
- ? Government/Industry Part Number = M83536/2 -026M
- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not suitable for lead free processing

#### Other:

- ? Brand = CII

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

