



**24-100-0** Bulk  
**24-100-2** Pkg (2)

Metal body RCA plug. Maximum cable dia. 7.5mm



**24-104-0** Bulk  
**24-104-2** Pkg (2)

Metal plug with strain relief. Maximum cable dia. 4.5mm



**24-101-0** Black  
**24-102-0** Red  
**24-109-4** Pkg (4)

Colored plastic body RCA plugs. Max. cable dia. 4.5mm.



**24-111-0** Black  
**24-112-0** Red  
**24-113-4** Pkg (4)

Colored plastic with strain relief. Max. cable dia. 4.5mm



**24-114-0** Bulk  
**24-114-2** Pkg (2)

Black plastic right angle RCA plug. Max. cable dia. 5.1mm




**24-116-0** Bulk  
**24-116-2** Pkg (2)

Crimp RCA plug for RG59/u



**24-118-0** Bulk  
**24-118-1** Pkg

Precision machined RCA plug for RG58/u




**24-120-0** Bulk  
**24-120-1** Pkg

Gold plated plug with spring strain relief. Cable dia 5.5mm



**24-121-0** Black  
**24-122-0** Red  
**24-123-2** Pkg (2)

Color coded gold plated plugs. Max. cable dia. 5.0mm



**24-124-0** Black  
**24-125-0** Red  
**24-126-2** Pkg (2)

Color coded gold plated plugs. Max cable dia. 6.0mm



**24-150-0** Bulk  
**24-150-2** Pkg (2)

Metal body RCA jack. Max. cable dia. 7.5mm



**24-151-0** Black  
**24-152-0** Red  
**24-159-2** Pkg (2)

Colored plastic RCA jacks. Max. cable dia. 5.0mm



**24-161-0** Black  
**24-162-0** Red  
**24-163-2** Pkg (2)

Gold plated color coded jacks. Max. cable dia. 5.0mm



**24-171-0** Bulk  
**24-171-6** Pkg (6)

Phenolic insulated RCA chassis jack. Mtg. holes 18mm C/C



**24-172-0** Bulk  
**24-172-2** Pkg (2)

22 x 56mm, 48mm C/C mtg. holes.

Phenolic insulated dual RCA jacks.




**24-180-0** Bulk  
**24-180-2** Pkg (2)

Chassis mount RCA jack. 6mm mounting hole.




**24-181-0** Bulk  
**24-181-2** Pkg (2)

Gold plated chassis RCA jack. 6mm mounting hole.




**24-182B-0** Black Bulk  
**24-182R-0** Red Bulk  
**24-182-2** Pkg (2)

Color coded chassis RCA jack. 8mm mtg hole.




**24-183B-0** Black Bulk  
**24-183R-0** Red Bulk  
**24-183-2** Pkg (2)

Gold Plated Color coded isolated chassis RCA jack. 8mm mtg hole.




**24-191-0** Bulk  
**24-191-2** Pkg (2)

PC mount RCA jack



**24-192-0** Bulk  
**24-192-2** Pkg (2)


PC mount RCA jack



**24-195-0** Bulk  
**24-195Y-0** Bulk  
**24-195-2** Pkg (2)

Right angle PC mount RCA jack

24-195-0 has a black insulator. 24-195Y-0 has a yellow insulator.



**24-196-0** Bulk  
**24-196-2** Pkg (2)

Right angle PC mount RCA jack