




## FUSEHOLDERS 10A @ 250VAC




Bayonet style fuse holder for 3AG (1/4" x 1 1/4") fuses.

**55-800-0** Bulk  
**55-800-1** Display Package



## 10A @ 250VAC




Pop-out style fuseholder for 3AG (1/4" x 1 1/4") fuses.

**55-801-0** Bulk  
**55-801-1** Display Package



## 10A @ 250VAC



Screw type fuseholder for 3AG (1/4" x 1 1/4") fuses.

**55-802-0** Bulk  
**55-802-1** Display Package

## INLINE FUSEHOLDER



Screw bakelite fuseholder for 3AG (1/4" x 1 1/4") fuses. 45cm of 12 AWG red wire. 20A @ 250VAC

**55-820-0** Bulk  
**55-820-1** Pkg


## INLINE FUSEHOLDER



Polypropylene fuseholder for 3AG (1/4" x 1 1/4") fuses. 19cm red 18AWG wire. 5A @ 250VAC.

**55-821-0** Bulk  
**55-821-1** Pkg

## FUSES



Standard 3AG size (1/4" x 1 1/4") fuses. Slow blow (MDL) & fast blow (AGC). Available in bulk only.

**Slow blow**  
**55-955-0** .5 Amp  
**55-970-0** 2 Amp

**Fast blow**  
**55-905-0** .5 Amp  
**55-910-0** 1 Amp  
**55-920-0** 2 Amp  
**55-925-0** 5 Amp  
**55-932-0** 15 Amp

**55-907-0** .75 Amp  
**55-915-0** 1.5 Amp  
**55-923-0** 3 Amp  
**55-930-0** 10 Amp  
**55-933-0** 20 Amp

## BATTERY HOLDERS



**4 x 'C'**  
**57-242-0** Bulk  
**57-242-1** Package



**2 x 'AA'**  
**57-322-0** Bulk  
**57-322-2** Package



**4 x 'AA'**  
**57-342-0** Bulk  
**57-342-2** Package



**4 x 'AA'**  
**57-343-0** Bulk  
**57-343-2** Package



**2 x 'AAA'**  
**57-422-0** Bulk  
**57-422-2** Package



**4 x 'AAA'**  
**57-442-0** Bulk  
**57-442-2** Package

## BATTERY SNAPS



57-901-0  
9 Volt battery snaps -  
24AWG 150mm long



57-902-0  
**57-901-0** 'I' type Bulk  
**57-902-0** 'T' type Bulk  
Use -10 for Display Package



9 Volt *molded* battery snaps -  
24AWG 150mm long

**57-902M-0** 'T' type Bulk  
Use -5 for Display Package