

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0002091103](#)  
**Status:** **Obsolete**  
**Overview:** [standard .093](#)  
**Description:** 2.36mm (.093") Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1189, Female, with Tin (Sn) Plated Brass Contact, 14-20 AWG, Bag, with Dimple  
**Replacement Part Number:**

**Documents:**  
[Drawing \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">1189</a>
Application	Power
Comments	with Dimple
Crimp Quality Equipment	Yes
Overview	<a href="#">standard .093</a>
Product Name	Standard .093"
Replacement Part Number	

**Physical**


Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Bag
Plating min - Mating	0.508µm (20µ")
Plating min - Termination	0.508µm (20µ")
Wire Insulation Diameter	1.65-4.06mm (.065-.160")
Wire Size AWG	14, 16, 18, 20
Wire Size mm <sup>2</sup>	N/A

**Material Info**

Old Part Number	1189-(P901)L
-----------------	--------------

**Reference - Drawing Numbers**

Product Specification	PS-02-09
Sales Drawing	SD-1189-**



**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[1189Series](#)

**Use With**

2629 , 1619 Plug or Receptacle Housing, 1545 Plug or Receptacle Housing, 1396 Plug or Receptacle Housing, 1490 Plug or Receptacle Housing, 1261 Plug or Receptacle Housing, 1292 Plug or Receptacle Housing, 1360 Plug or Receptacle Housing, 1375 Plug or Receptacle Housing, 2163 Plug or Receptacle Housings

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool	<a href="#">0638191100</a>
Extractor Tool for .093 and	<a href="#">0638240200</a>

This document was generated on 05/13/2011

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**