

KNOB



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6

Control Knobs

Retail Part No.	Quantity per Package	Figure No.	Description	Outer Diameter (Inches)	Height (Inches)	Shaft Size (Inches)	Recessed for Locknut	Brass Insert
790-1126	1	1	Round Skirted Control Knob	1 1/2	11/16	1/4	Yes	No
WA-1600	1	1	Round Skirted Control Knob	1 1/2	9/16	1/4	Yes	No
WA-1600-P	5	1	Round Skirted Control Knob	1 1/2	9/16	1/4	Yes	No
WA-1600A	1	1	Round Skirted Control Knob	1 1/2	9/16	1/4	Yes	Yes
WA-1600A-P	5	1	Round Skirted Control Knob	1 1/2	9/16	1/4	Yes	Yes
WA-1610A	1	1	Round Skirted Control Knob	1	9/16	1/4	Yes	Yes
790-1124	1	2	Bar Control Knob	1 1/8	9/16	1/4	Yes	No
WA-1500	1	2	Bar Control Knob	1 1/8	9/16	1/4	Yes	No
WA-1500-P	5	2	Bar Control Knob	1 1/8	9/16	1/4	Yes	No
WA-1510	1	2	Bar Control Knob	3/4	9/16	1/4	Yes	No
WA-1510-P	5	2	Bar Control Knob	3/4	9/16	1/4	Yes	No
WA-1520	1	2	Bar Control Knob	1 1/2	3/4	1/4	Yes	No
WA-1520-P	5	2	Bar Control Knob	1 1/2	3/4	1/4	Yes	No

Lever Knobs

Retail Part No.	Quantity per Package	Figure No.	Description	Length (Inches)	Height (Inches)	Shaft Size (Inches)	Recessed for Locknut	Brass Insert
WA-2110A	1	3	Short Lever Knob	1 5/8	19/32	1/4	Yes	Yes
WA-2100A	1	3	Long Lever Knob	2 1/2	5/8	1/4	Yes	Yes
WA-2100A-P	5	3	Long Lever Knob	2 1/2	5/8	1/4	Yes	Yes

Instrument Knobs

Retail Part No.	Quantity per Package	Figure No.	Description	Outer Diameter (Inches)	Height (Inches)	Shaft Size (Inches)	Recessed for Locknut	Brass Insert
790-1051	1	4	Fluted Skirted Instrument Knob	3/4	1/2	1/4	Yes	No
790-1052	1	4	Fluted Skirted Instrument Knob	1 1/8	5/8	1/4	Yes	No
WA-101	1	4	Fluted Skirted Instrument Knob	3/4	1/2	1/4	Yes	No
WA-101-P	5	4	Fluted Skirted Instrument Knob	3/4	1/2	1/4	Yes	No
WA-101C	1	4	Fluted Skirted Instrument Knob	3/4	1/2	1/4	Yes	No
WA-101C-P	5	4	Fluted Skirted Instrument Knob	3/4	1/2	1/4	Yes	No
WA-102	1	4	Fluted Skirted Instrument Knob	1 1/8	5/8	1/4	Yes	No
WA-102-P	5	4	Fluted Skirted Instrument Knob	1 1/8	5/8	1/4	Yes	No
WA-102B	1	4	Fluted Skirted Instrument Knob	1 1/8	5/8	1/4	Yes	Yes
WA-102B-P	5	4	Fluted Skirted Instrument Knob	1 1/8	5/8	1/4	Yes	Yes
WA-103	1	4	Fluted Skirted Instrument Knob	1 1/4	3/4	1/4	Yes	No
WA-103-P	5	4	Fluted Skirted Instrument Knob	1 1/4	3/4	1/4	Yes	No
WA-103B	1	4	Fluted Skirted Instrument Knob	1 1/4	3/4	1/4	Yes	Yes
WA-103B-P	5	4	Fluted Skirted Instrument Knob	1 1/4	3/4	1/4	Yes	Yes
WA-104	1	4	Fluted Skirted Instrument Knob	1 1/2	7/8	1/4	Yes	No
WA-104-P	5	4	Fluted Skirted Instrument Knob	1 1/2	7/8	1/4	Yes	No
WA-104B	1	4	Fluted Skirted Instrument Knob	1 1/2	7/8	1/4	Yes	Yes
WA-105B	1	4	Fluted Skirted Instrument Knob	2	15/16	1/4	Yes	Yes
WA-105B-P	5	4	Fluted Skirted Instrument Knob	2	15/16	1/4	Yes	Yes
WA-106S	1	5	Fluted Skirted Instrument Knob, with Silver Inlay	1 1/4	3/4	1/4	Yes	No
WA-4100	1	6	Fully Fluted Stemmed Instrument Knob	1 1/8	5/8	1/4	Yes	Yes
WA-4100-P	5	6	Fully Fluted Stemmed Instrument Knob	1 1/8	5/8	1/4	Yes	Yes
WA-4100D	1	6	Fully Fluted Stemmed Instrument Knob	1 1/8	5/8	1/4	No	Yes
WA-4101	1	6	Fully Fluted Stemmed Instrument Knob	1 3/8	11/16	1/4	Yes	Yes
WA-4102	1	6	Fully Fluted Stemmed Instrument Knob	1 5/8	3/4	1/4	Yes	Yes
WA-4103	1	6	Fully Fluted Stemmed Instrument Knob	2 3/8	7/8	1/4	Yes	Yes
WA-4103-P	5	6	Fully Fluted Stemmed Instrument Knob	2 3/8	7/8	1/4	Yes	Yes



Instrument Knobs (Continued)

Retail Part No.	Quantity per Package	Figure No.	Description	Outer Diameter (Inches)	Height (Inches)	Shaft Size (Inches)	Recessed for Locknut	Brass Insert
WA-4104	1	1	Fully Fluted Skirted/Stemmed Instrument Knob	1 1/2	51/64	1/4	Yes	Yes
WA-4107	1	1	Fully Fluted Skirted/Stemmed Instrument Knob	1 3/4	7/8	1/4	Yes	Yes
WA-4108	1	1	Fully Fluted Skirted/Stemmed Instrument Knob	2 1/16	7/8	1/4	Yes	Yes
WA-4108-P	5	1	Fully Fluted Skirted/Stemmed Instrument Knob	2 1/16	7/8	1/4	Yes	Yes
WA-4109	1	1	Fully Fluted Skirted/Stemmed Instrument Knob	3	1	1/4	Yes	Yes
WA-4109-P	5	1	Fully Fluted Skirted/Stemmed Instrument Knob	3	1	1/4	Yes	Yes
WA-1200	1	2	Round Instrument Knob, with Silver Inlay	1/2	5/8	1/4	No	No
WA-1200-P	5	2	Round Instrument Knob, with Silver Inlay	1/2	5/8	1/4	No	No
WA-1202	1	2	Round Instrument Knob, with Silver Inlay	3/4	5/8	1/4	Yes	No
WA-1202-P	5	2	Round Instrument Knob, with Silver Inlay	3/4	5/8	1/4	Yes	No
WA-1204	1	2	Round Instrument Knob, with Silver Inlay	1	11/16	1/4	Yes	No
WA-1204-P	5	2	Round Instrument Knob, with Silver Inlay	1	11/16	1/4	Yes	No
WA-1208	1	2	Round Instrument Knob, with Silver Inlay	1 3/4	13/16	1/4	Yes	No
WA-1208-P	5	2	Round Instrument Knob, with Silver Inlay	1 3/4	13/16	1/4	Yes	No
WA-1450	1	3	Round Instrument Knob	11/16	13/32	1/4	No	No
WA-1450G	1	3	Round Instrument Knob	11/16	13/32	1/8	No	No
WA-1475	1	3	Round Instrument Knob	1	1/2	1/4	Yes	No
WA-1475-P	5	3	Round Instrument Knob	1	1/2	1/4	Yes	No
790-1303	1	4	Round Military Instrument Knob	3/4	5/8	1/4	Yes	Yes
790-1308	1	5	Round Skirted Military Instrument Knob	1/2	11/16	1/8	Yes	Yes
790-1335	1	5	Round Skirted Military Instrument Knob	3/4	3/4	1/4	Yes	Yes
790-1260	1	6	Round Skirted Instrument Knob, with Silver Inlay	1/2	11/16	1/8	Yes	Yes
790-1261	1	6	Round Skirted Instrument Knob, with Silver Inlay	3/4	13/16	1/4	Yes	Yes

Pointer Knobs

Retail Part No.	Quantity per Package	Figure No.	Description	Length (Inches)	Height (Inches)	Shaft Size (Inches)	Recessed for Locknut	Brass Insert
WA-1210	1	7	Pointer Knob, with Silver Inlay	1	5/8	1/4	Yes	No
WA-1210-P	5	7	Pointer Knob, with Silver Inlay	1	5/8	1/4	Yes	No
790-1132	1	8	Round Pointer Knob	1 1/8	5/8	1/4	Yes	Yes
WA-1550	1	8	Round Pointer Knob	1 1/8	9/16	1/4	Yes	No
WA-1550-P	5	8	Round Pointer Knob	1 1/8	9/16	1/4	Yes	No
WA-2150	1	9	Flat-top Pointer Knob	1 1/4	9/16	1/4	Yes	No
WA-109	1	10	Fluted "Chicken Head" Pointer Knob	1 1/4	5/8	1/4	Yes	No
WA-109-P	5	10	Fluted "Chicken Head" Pointer Knob	1 1/4	5/8	1/4	Yes	No
WA-109B	1	10	Fluted "Chicken Head" Pointer Knob	1 1/4	5/8	1/4	Yes	Yes
790-1204	1	11	Ridge-top "Chicken Head" Pointer Knob	1 1/4	5/8	1/4	Yes	Yes
WA-2300	1	11	Ridge-top "Chicken Head" Pointer Knob	1 1/4	5/8	1/4	Yes	Yes
WA-2300A	1	11	Ridge-top "Chicken Head" Pointer Knob	1 1/4	5/8	1/4	Yes	No
790-1208	1	12	Ridge-top "Chicken Head" Pointer Knob, Elongated	2	5/8	1/4	Yes	Yes
WA-2350	1	12	Ridge-top "Chicken Head" Pointer Knob, Elongated	2	5/8	1/4	Yes	No

KNOBS (Cont.)



Fig. 1



Fig. 2



Fig. 3

Miscellaneous Knobs

Retail Part No.	Quantity per Package	Figure No.	Description	Outer Diameter (Inches)	Height (Inches)	Shaft Size (Inches)	Recessed for Locknut	Brass Insert
6126	1	1	Push/Pull Knob	5/8	7/16	1/4	No	Yes
30-5002-19R	1	2	Switch Knob	9/16 x 9/32	7/16	1/8 Square	No	No
790-1285	1	3	Single Bar Knob, with Silver Inlay	1/2	1/2	1/8	Yes	Yes