

Ring cable lug - C-RC 95/M8 DIN



3240120

<https://www.phoenixcontact.com/pc/products/3240120>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Ring cable lug, non-insulated, 95 mm², M8

Your advantages

- The CRIMPFOX-RC... tools from our CRIMPFOX range of crimping pliers are available for optimum crimping
- The hard-soldered press zone enables maximum conductor pull-out values to be achieved
- The ring cable lugs without plastic sleeve are made from high-quality tin-plated electrolytic copper for maximum protection against corrosion

Commercial Data

Item number	3240120
Packing unit	50 pc
Minimum order quantity	50 pc
Product Key	BH3422
Catalog Page	Page 491 (C-3-2019)
GTIN	4046356453370
Weight per Piece (including packing)	41.66 g
Weight per Piece (excluding packing)	40 g
Customs tariff number	85369010
Country of origin	CN

Ring cable lug - C-RC 95/M8 DIN

3240120

<https://www.phoenixcontact.com/pc/products/3240120>




Technical Data

Product properties

Product type	Connector
--------------	-----------

Dimensions

Dimensional drawing	
Width	24 mm
Length	54 mm
Length of the insulating material sleeve	20 mm
Maximum stripping length	23 mm
Distance from the center to the insulating material sleeve	22 mm
Min. material thickness	2.5 mm
Inner dimensions of the insulating collar	15 mm

Internal dimensions

Internal diameter	8.4 mm
-------------------	--------

Material specifications

Color	silver
Material	Copper
Coating	tin-plated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	110 °C
---------------------------------	--------

Standards and regulations

Design according to standard	DIN 46234
------------------------------	-----------

Ring cable lug - C-RC 95/M8 DIN


3240120

<https://www.phoenixcontact.com/pc/products/3240120>



Drawings

Dimensional drawing



Ring cable lug - C-RC 95/M8 DIN



3240120

<https://www.phoenixcontact.com/pc/products/3240120>

Classifications

ECLASS

ECLASS-9.0	27400204
ECLASS-10.0.1	27400204
ECLASS-11.0	27400204

ETIM

ETIM 8.0	EC001052
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

Ring cable lug - C-RC 95/M8 DIN



3240120

<https://www.phoenixcontact.com/pc/products/3240120>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com