




TOPJOB® S




Double-Deck Terminal Blocks 2.5 (4) mm²

2002 Series

0.25 ... 2.5 (4) mm ² ① 500 V/6 kV/3 ② I _N 24 A (28 A)	AWG 22 ... 12 600 V, 20 A ④ 600 V, 20 A ⑤	0.25 ... 2.5 (4) mm ² ① 500 V/6 kV/3 ② I _N 24 A (28 A)	AWG 22 ... 12 600 V, 20 A ④ 600 V, 20 A ⑤	0.25 ... 2.5 (4) mm ² ① 500 V/6 kV/3 ② I _N 24 A (28 A)	AWG 22 ... 12 600 V, 20 A ④ 600 V, 20 A ⑤
Terminal block width 5.2 mm / 0.205 in. □ 10 ... 12 mm / 0.43 in. ③		Terminal block width 5.2 mm / 0.205 in. □ 10 ... 12 mm / 0.43 in. ③		Terminal block width 5.2 mm / 0.205 in. □ 10 ... 12 mm / 0.43 in. ③	



Item No.	Pack. Unit	Item No.	Pack. Unit	Item No.	Pack. Unit
Through/through terminal block, with marker carrier, gray housing		Through/through terminal block, with marker carrier, blue housing		Ground conductor/through terminal block, with marker carrier, gray housing	
○ L/L ⑤	2002-2231 ⑤ 50	● N/N ⑤	2002-2234 ④ ⑤ 50	○ PE/N ⑤	2002-2247 ⑤ 50
○ N/L ⑤	2002-2232 ⑤ 50			○ PE/L ⑤	2002-2257 ⑤ 50
○ L/N ⑤	2002-2233 ⑤ 50				
Through/through terminal block, without marker carrier, gray housing		Through/through terminal block, without marker carrier, blue housing		Ground conductor/through terminal block, without marker carrier, gray housing	
○ L/L ⑤	2002-2201 ⑤ 50	● N/N ⑤	2002-2204 ④ ⑤ 50	○ PE/N ⑤	2002-2217 ⑤ 50
○ N/L ⑤	2002-2202 ⑤ 50			○ PE/L ⑤	2002-2227 ⑤ 50
○ L/N ⑤	2002-2203 ⑤ 50				
Other terminal blocks with the same profile:					
Diode	2002-2211/1000-410	Page86			
LED	2002-2221/1000-434	Page86			



Item No.	Pack. Unit	Item No.	Pack. Unit	Item No.	Pack. Unit
4-conductor through terminal block, with marker carrier, internal commoning, conductor entry position colored in violet, gray housing		4-conductor through terminal block, with marker carrier, internal commoning, conductor entry position colored in violet, blue housing		4-conductor ground terminal block, with marker carrier, internal commoning, green-yellow housing	
○ L ⑤	2002-2238 ⑤ 50	● N ⑤	2002-2239 ④ ⑤ 50	● PE ⑤	2002-2237 ⑤ 50
4-conductor through terminal block, without marker carrier, internal commoning, conductor entry position colored in violet, gray housing		4-conductor through terminal block, without marker carrier, internal commoning, conductor entry position colored in violet, blue housing		4-conductor ground terminal block, without marker carrier, internal commoning, green-yellow housing	
○ L ⑤	2002-2208 ⑤ 50	● N ⑤	2002-2209 ④ ⑤ 50	● PE ⑤	2002-2207 ⑤ 50