

TS 35X7.5 2M/ST/SZ**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image

Similar to illustration

Steel DIN rails are the most widespread on the market.
Among metal DIN rails, they have the lowest shortcircuit
protection, similar to stainless steel.

General ordering data

Version	Rail, TS 35, TS 35 x 7.5, without slot, Steel, galvanic zinc plated and passivated
Order No.	9300090000
Type	TS 35X7.5 2M/ST/SZ
GTIN (EAN)	4032248387564
Qty.	2 m

TS 35X7.5 2M/ST/SZ

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.295 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	327.5 g		

Mounting rail

Installation advice		Direct mounting	
Length of the terminal rail	nominal	2,000 mm	
	min.	0 mm	
	max.	2,000 mm	
Material	Steel		
Pre-punched mounting rail	No		
Short circuit strength corresponds to E-Cu wire	16 mm²		
Short-time withstand current according to IEC 60947-7-2	1.92 kA/1s		
Slit gap			
Slit length			
Slit width			
Standards	DIN EN 60715		
Surface finish	galvanic zinc plated and passivated		
Thickness	1 mm		

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02

Important note

Product information	Din rails with Sendzimier treatment have limited corrosion resistance on the outer and cut edges
---------------------	--

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Storage Conditions Terminal Blocks
Catalogues	Catalogues in PDF-format

TS 35X7.5 2M/ST/SZ

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Drawings

Product image

