

**Accessories**  
**G 20/0.25A/F****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	G 20/0.25A/F
Order No.	<a href="#">0430500000</a>
Version	Active components, Fuse
GTIN (EAN)	4008 19015399 1
Qty.	10 pc(s).

**Accessories**  
**G 20/0.25A/F**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	5 mm	Width (inches)	0.197 inch
Height	20 mm	Height (inches)	0.787 inch
Depth	5 mm	Depth (inches)	0.197 inch
Net weight	0.9 g		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Material data**

Colour	Light Grey
--------	------------

**System specifications**

Version	Fuse accessories
---------	------------------

**Fuse cartridges**

Cartridge fuse	G-Si. 5 x 20	Characteristics	quick-acting
Colour	Light Grey	Current	0.25 A
Melting integral	0.07 A <sup>2</sup> s	Power output (@ 1.5 In)	0.3 W
Rated breaking capacity	1.5 kA	Version	Fuse accessories
Voltage drop	280 mV		

**Rating data**

Rated voltage	250 V	Rated current	0.25 A
---------------	-------	---------------	--------

**Classifications**

ETIM 6.0	EC000035	ETIM 7.0	EC000035
eClass 9.0	27-14-20-01	eClass 9.1	27-14-20-01
eClass 10.0	27-14-20-01		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN.WSCAD</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>