



60599-1 Product Details

 [Share](#)  [Print](#)  [Email](#)



60599-1

TE Internal Number: 60599-1

 [Active](#)

 [View 3D PDF](#)

Printed Circuit Board Disconnects

[Not EU RoHS or ELV Compliant \(Find RoHS Compliant Alternates\)](#)

Product Highlights:

- Contact Type = Pin
- A Body Shape
- Hole Diameter = 1.50 - 1.57 mm
- Disconnect Diameter = 1.47 mm
- Without Insulation Support

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [PIN, .058 DIAMETER, BRASS, KNURLED, P.C. CONTACT](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [.058 Diameter Printed Circuit Board Disconnect System](#) (PDF, English)

Application Specifications:

- [.058 and .093 Diameter Printed Circuit Board Pins an...](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version S)
- [3D Model](#) (IGES, Version S)
- [3D Model](#) (STEP, Version S)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Body Shape](#) = A
- [Insulation Support](#) = No
- Material = Brass

Body Features:

- [Hole Diameter \(mm \[in\]\)](#) = 1.50 - 1.57 [0.059 - 0.062]
- [Disconnect Diameter \(mm \[in\]\)](#) = 1.47 [0.058]

Contact Features:

- [Contact Type](#) = Pin
- Plating Material = Tin

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Packaging Features:

- [Packaging Method](#) = Loose Piece

Other:

- Brand = AMP

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference Products](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates



