

I.D. PRO® Plus, Brady LS2000, BradyMarker™ XC Plus Labels

CONTINUED


PRINTER MODEL

PRO = ID PRO/PRO Plus

LS = LS2000

BMXC = BradyMarker XC Plus


ALL = All ID PRO, LS2000, BMXC



► BRADYTAG® PRINTABLE TAGS

White Polyester (B-620)

Part Number	Portable Printer Model	Tags Per Roll	Tag Dimension Inch (mm)		Maximum Lines of Print (LS/BMXC)	Maximum Characters Across Large (LS/BMXC)	Small (LS/BMXC)
			A	B			
WMT-313-620	LS/BMXC	500	1.750 (44.45)	0.625 (15.88)	3/3	8/8	17/17
WMT-713-620	LS/BMXC	250	1.750 (44.45)	1.125 (28.58)	7/7	8/8	17/17




► TERMINAL BLOCK MARKERS

White Vinyl Cloth (B-502)

Part Number	Portable Printer Model	Roll Length Ft. (m)	Label Width Inch (mm) A	Label Height Inch (mm) B	Maximum Lines of Print	Maximum Characters Across Large	Small
TB03-502-281	LS	30 ft (9.14 m)	0.281 (7.14)	30 ft (9.14 m)	1	1	3
TB03-502-312	LS	30 ft (9.14 m)	0.312 (7.92)	30 ft (9.14 m)	1	1	3
TB05-502-375	LS	30 ft (9.14 m)	0.375 (9.53)	30 ft (9.14 m)	1	2	5

*First two digits of size code may change, depending on number of lines you need on your marker.
(Example: entering 0403 would give you 4 lines of half height or 2 lines of normal height print.)



► PERMASHIELD™ LABELS

White Paper (B-122), White Polyester (B-619), Metallized Polyester (B-969)

Part Number	Portable Printer Model	Labels Per Roll	Marker Label Material	Label Width Inch (mm) A	Label Height Inch (mm) B	Overlamine Inch (mm) C	Dimensions D	Maximum Lines of Print (PRO/LS)	Maximum Characters Across Large (PRO/LS)	Small (PRO/LS)
PSL-311-122	ALL	250	Paper	1.000 (25.40)	0.500 (12.70)	1.060 (26.92)	0.750 (19.05)	3/3	7/7	10/15
PSL-311-619	ALL	250	Polyester	1.000 (25.40)	0.500 (12.70)	1.060 (26.92)	0.750 (19.05)	3/3	7/7	10/15
PSL-311-969	ALL	250	Metallized Polyester	1.000 (25.40)	0.500 (12.70)	1.060 (26.92)	0.750 (19.05)	3/3	7/7	10/15
PSL-514-619	LS	250	Polyester	1.250 (31.75)	0.750 (19.05)	1.500 (38.10)	1.000 (25.40)	5	9	19
PSL-514-969	LS	250	Metallized Polyester	1.250 (31.75)	0.750 (19.05)	1.500 (38.10)	1.000 (25.40)	5	9	19
PSL-1833-619-BK	LS	250	Polyester	2.250 (57.15)	1.250 (31.75)	2.500 (63.50)	1.500 (38.10)	9	16	33
PSL-1833-969-BK	LS	250	Metallized Polyester	2.250 (57.15)	1.250 (31.75)	2.500 (63.50)	1.500 (38.10)	9	16	33

* This product is sold in Japan only under the Overlamine Labels name and not under the PermaShield name.

PORTABLE
PRINTERS AND LABELS

WIRE & CABLE MARKING

I.D. PRO PLUS / BRADY LS2000 LABELS