



[Labels](#) / [Labels by Application](#) / [Wire and Cable Labels](#) / [Wire and Cable Label Cards](#) /

Pre-printed 2 Wire Markers



Pre-printed 2 Wire Markers

Part Number:

HH-2-PK

Dimensions:

1.5 in H

Material:

Cloth

Color:

Black on White

Text Legend:

2

ADD TO CART

1



Add To Favorites

Free sample pack  Download
guide 

PEOPLE ALSO VIEWED

OVERVIEW

Made of B-12 matte white acetate cloth, these HH series wire markers are oil and heat resistant making them perfect for withstanding varnish dip or baking cycles.

SPECIFICATIONS

Material Number	B-12
Cards or Sheets per Pack	25
Dimensions	1.5 in H
UOM	Pack
Finish	Matte
Maximum Service Temperature °F	221 °F
Minimum Service Temperature °F	-40 °F
Product Number	111192
UPC	662820902249
Quantity per Card or Sheet	36
Thickness	0.008 in
Adhesive Type	Rubber

Applications	Cable & Wire Marking
Color	Black on White
Label/Media Format	Die-Cut on Cards
Label Properties	Harsh Environment Labels, Heat Resistant Labels, Permanent Adhesive Labels
Material	Cloth
Material Properties	Rigid
Resistance Properties	Corrosion-Resistant, Heat-Resistant, Humidity-Resistant, Oil-Resistant, UV-Resistant
Serialization	No Serialization
Text Legend	2

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Visual Workplace Services](#)
[Hazcom GHS Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Design Custom Safety Signs](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)
[EPA e-Manifest Update](#)

Corporate


[About](#)
[Careers](#)
[Investors](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO Certificates](#)

Other BradyContact Sites

[Distributor Portal](#)
[International Sites](#)
[Safety Services & Software](#)
[Smart ID Brand Protection Solutions](#)

6555 W. Good Hope Rd. Milwaukee, WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CT Monday - Thursday; Friday 7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 © Brady Worldwide, Inc.