


[Home](#) > [Products](#) > [By Type](#) > [Product Feature Selector](#) > Product Details

160530-1 Product Details

 [Live Product Chat](#)



160530-1

TE Internal Number: 160530-1

 [Obsolete](#)

[Contact Product Information Center](#)

Ring and Spade Tongue Terminals

[Not reviewed for RoHS Compliance](#)

Product Highlights:

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Barrel Type = Open Barrel
- Wire/Cable Type = Tinsel Wire
- Uninsulated

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [Automachine and General Products](#) (PDF, English)

Product Specifications:

- [Terminal, AMPLIVAR, Ring, Crimping](#) (PDF, English)
- [Terminal, Ring, Extruded, Crimping](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Terminal Shape](#) = Ring Tongue
- [Receptacle Style](#) = Straight
- [Barrel Type](#) = Open Barrel
- [Wire/Cable Type](#) = Tinsel Wire
- [Insulation](#) = No
- [Insulation Support](#) = Insulation Piercing
- [Insulation Diameter \(mm \[in\]\)](#) = 2.40-2.90 [.094-.114]
- [Stud Diameter \(mm \[in\]\)](#) = 3.00 [0.118]
- Stud Size = None
- [Shape](#) = RING-071
- [Heavy Duty](#) = No
- [Material](#) = Brass
- Finish = None

Body Related Features:

- Stock Thickness (mm [in]) = 0.30 [0.012]

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

Packaging Related Features:

- [Packaging Method](#) = Strip

Other:

- Brand = AMP

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)