



HUBBELL iStation AV Modules, Gold RCA Composite, Feed-Thru

iSTATION™ Front-Loading
Footprint.

Seamless Hubbell System
Integration.

Transmits High Quality
Composite Audio/Video Signal.

High Quality Gold-Plating.

High performance Gold-
plated speaker post.



Quick, easy plug 'n play
style installation.

High impact, flame-re-
tardant Polymer.

SPECIFICATIONS

- ◆ **Connector:**
Connector Body: Brass.
Gold-plated: 2μ"
- ◆ **Performance:**
Impedance: 75 Ohms.
Mating Cycles: 500+
- ◆ **Material:**
Module:
Flame-retardant Polymer UL 94V-0.
- ◆ **Insulator Color:** Yellow, Red and White.

Hubbell's iSTATION™ composite RCA feed-thru modules deliver high quality A/V signals to work areas or transmitting/receiving devices. The composite RCA feed-thru modules utilize 20-30 AWG coaxial cable to deliver composite A/V signal within a horizontal point-to-point run.

iSTATION™ component RCA feed-thru modules are available in 7 standard Hubbell colors and front loads into any iSTATION™ product, Hubbell Delivery System products including poke-throughs and surface raceway, or iSTATION™ UDX multimedia panels to distribute composite A/V signals. Requiring a standard RCA patch cord, these connectors install with a snap.

Create a customized multimedia work station by front-loading a iSTATION™ Gold RCA composite module along with Hubbell's extensive line of AV connectors, loaded modules and XCELERATOR™ jacks.

CABLE TERMINATION

Cable Type: Coax 75 Ohm - RG6, RG59, Mini-Coax, RCA Patch Cords.

APPLICATIONS SUPPORTED

- Composite video distribution with audio.
- TV, CCTV, CATV and satellite.
- Home theater and entertainment systems.
- Cameras, camcorders and projectors.
- Security and surveillance systems.

CONNECTOR TERM

RCA Connector: The standard connector used in line-level consumer and studio sound equipment. RCA connectors supply unbalanced signal and are used in almost all systems and between almost all audio/video components. They are used for inter-connecting Composite, Component and Digital coaxial audio video signals.

INSTALLATION TIPS

Important: Always allow for clearance behind connection location to ensure for proper bend radius.

Termination: Connection is a "push-on" RCA connector (patch cord).


Gold-plating encapsulates the connectors base metal (brass) preventing oxidation/corrosion from forming. It also has a more transparent (increased signal transfer) conductive path over Nickel (3x).

**iSTATION™ RCA Composite, Feed-thru AV Modules**

See RCA Insulator Color Chart for applications.



Description Catalog No.
 RCA (3) Composite Coupler, Feed-thru Module **IM3RF1XX**
XX = Color: "AL" = Almond; "BK" = Black; "EI" = Electric Ivory;
 "GY" = Gray; "LA" = Light Almond; "OW" = Office White;
 "W" = White.

DIMENSIONS**RCA INSULATOR COLOR: APPLICATIONS**


Color	Audio	Video
Red	Right Signal	Component - Red (Pr/Cr)
White	Left Signal	
Yellow		Composite
Blue		Component - Blue (Pb/Cb)
Green		Component - Green (Y)
Black	Mono/Right	
Orange	Digital (S/PDIF)	Digital (S/PDIF)

iSTATION™ COMPATIBLE**Work Station and Cross-Connect Solutions**

- iSTATION™ front-loading plates
- UDX iSTATION™ Multimedia Panels

Hubbell Delivery System

- Hubbell SystemOne Poke-Thrus and Floor Boxes
- Hubbell Surface Raceway, Metal and Non-Metallic
- Multi-Connect™ Wall Boxes/Conference Table Boxes
- Power Poles

**TYPICAL APPLICATION**

— Patch Cords
 — Horizontal Cable

RCA composite module/
 connector in a Hubbell
 iSTATION™ face plate.

**Hubbell Premise Wiring**

HUBBELL INCORPORATED (Delaware)
 14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005
 Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

Worldwide Locations

Hubbell Premise Wiring, Asia Pacific
 Hubbell Canada Inc.
 Hubbell Premise Wiring, Central America
 Hubbell Premise Wiring, China
 Hubbell Premise Wiring, Europe
 Hubbell Premise Wiring, India
 Hubbell Int'l. Inc., Korea Branch

852-2836-7131
 905-839-1138
 506-309-4158
 86-21-6374 2660
 44-01283 500500
 91-80-4022-4089
 (82 2) 2607 1363

Fax: 852-2836-7132
 Fax: 905-839-9108
 Fax: 506-260-1616
 Fax: 86-21-6374 2799
 Fax: 44-01283 500400
 Fax: 91-80-4022-4033
 Fax: (82 2) 2603 7386

Hubbell Premise Wiring, Latin America
 Hubbell de Mexico, S.A. de C.V.
 Hubbell Premise Wiring, Middle East
 Hubbell Premise Wiring, Puerto Rico
 Hubbell-Taian Co., Ltd., Taiwan
 Hubbell Premise Wiring, Venezuela

305-408-4501
 (5255) 9151-9999
 971-4-393-4192
 787-855-1075
 886-2-2522-1862
 58-212-5156482

Fax: 305-408-8201
 Fax: (5255) 9151-9989
 Fax: 971-4-393-4194
 Fax: 787-855-3265
 Fax: 886-2-2522-1872
 Fax: 58-212-6627258