

Double Row Terminal Blocks

Kulka® 600 GP Series

300 Volts AC/DC (Class B)
150 Volts AC/DC (Class C)



600 GP 07 PSB

Specifications:

- Base, Phenolic, 150°C (UL RTI)
- Open Back Design (Insulator Strip required for Voltage Rating - see page 112)
- JJ (GDI-30F) Material Available
- Screws, #5-40 Binder Head, Phil-Slot, Brass
- Terminals, Plated Brass
- 1-22 Poles
- 3/8" Centers
- Wire Range With Wire Binding Screw
#14 - #22 AWG – 15 Amps
- UL Recognized File No. XCFR2.E47811
- CSA Certified File No. LR19766
- **CE**
- RoHS Compliant

Kulka® Catalog #	# of poles	Dimensions	
		A	B
600 GP 01 PSB	1	1.03	0.75
600 GP 02 PSB	2	1.41	1.13
600 GP 03 PSB	3	1.78	1.50
600 GP 04 PSB	4	2.16	1.88
600 GP 05 PSB	5	2.53	2.25
600 GP 06 PSB	6	2.91	2.63
600 GP 07 PSB	7	3.28	3.00
600 GP 08 PSB	8	3.66	3.38
600 GP 09 PSB	9	4.03	3.75
600 GP 10 PSB	10	4.41	4.13
600 GP 11 PSB	11	4.78	4.50
600 GP 12 PSB	12	5.16	4.88
600 GP 13 PSB	13	5.53	5.25
600 GP 14 PSB	14	5.91	5.63
600 GP 15 PSB	15	6.28	6.00
600 GP 16 PSB	16	6.66	6.38
600 GP 17 PSB	17	7.03	6.75
600 GP 18 PSB	18	7.41	7.13
600 GP 19 PSB	19	7.78	7.50
600 GP 20 PSB	20	8.16	7.88
600 GP 21 PSB	21	8.53	8.25
600 GP 22 PSB	22	8.91	8.63

mm=dim X 25.4

For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html

Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

CATALOG #	PRODUCT DESCRIPTION	PAGE REFERENCE
MSP KT19	Full Quick Connect (0° Flat)	See Page 105
KULKA KT20	Full Quick Connect (45° Bend)	See Page 105
KT21	Full Quick Connect (90° Bend)	See Page 105
KT25	Half Quick Connect (0° Flat)	See Page 105
KT26	Half Quick Connect (45° Bend)	See Page 105
KT27	Half Quick Connect (90° Bend)	See Page 105
ST	Full Solder	See Page 106
3/4 ST	Half Solder	See Page 106
Y	Feed Thru Solder (.312)	See Page 106
YSY	Feed Thru Solder (.500)	See Page 106
Z	Lug Over the Side (.625)	See Page 106
J 600	Line to Line Jumper	See Page 107
600 RJ(S)	Multiple Position Jumper	See Page 107
2004	Feed Thru Solder	See Page 109

Quick Connects: .020" x .187"

See pages 104-115 for terminal block accessories

