

Double Row Terminal Blocks

Kulka® 602/802 GP Series

300 Volts AC/DC (Classes B/C)

602 Series only

150 Volts AC/DC (Class C)

802 Series only



602 GP 06

Specifications:

- Base, General Purpose Phenolic, 150°C (UL RTI)
- Open Back Design (Insulator Strip required for Voltage Rating - see page 112)
- JJ (GDI-30F) Material Available
- Screws, #8-32 Binder Head, Phil-Slot, Steel
- Terminals, Plated Brass
- 1-26 Poles
- 9/16" Centers
- Wire Range With Wire Binding Screw #10 - #18 AWG – 30 Amps
- 802 Series (Riveted KT's) - see page 105
- UL Recognized File No. XCFR2.E47811
- CSA Certified File No. LR19766
- CE
- RoHS Compliant

Double Row Terminal Blocks

Kulka® Catalog #	# of poles	Dimensions	
		A	B
602 GP 01	1	1.54	1.13
602 GP 02	2	2.10	1.69
602 GP 03	3	2.66	2.25
602 GP 04	4	3.22	2.81
602 GP 05	5	3.79	3.38
602 GP 06	6	4.35	3.94
602 GP 07	7	4.91	4.50
602 GP 08	8	5.47	5.06
602 GP 09	9	6.04	5.63
602 GP 10	10	6.60	6.19
602 GP 11	11	7.16	6.75
602 GP 12	12	7.72	7.31
602 GP 13	13	8.29	7.88
602 GP 14	14	8.85	8.44
602 GP 15	15	9.41	9.00
602 GP 16	16	9.97	9.56
602 GP 17	17	10.54	10.13
602 GP 18	18	11.10	10.69
602 GP 19	19	11.66	11.25
602 GP 20	20	12.22	11.81
602 GP 21	21	12.79	12.38
602 GP 22	22	13.35	12.94
602 GP 23	23	13.91	13.50
602 GP 24	24	14.47	14.06
602 GP 25	25	15.04	14.63
602 GP 26	26	15.60	15.19

mm=dim X 25.4

For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html

Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

CATALOG # MSP	KULKA PRODUCT DESCRIPTION	PAGE REFERENCE
	KT55 Full Quick Connect (0° Flat)	See Page 105
	KT56 Full Quick Connect (45° Bend)	See Page 105
	KT57 Full Quick Connect (90° Bend)	See Page 105
	KT61 Half Quick Connect (0° Flat)	See Page 105
	KT62 Half Quick Connect (45° Bend)	See Page 105
	KT63 Half Quick Connect (90° Bend)	See Page 105
	ST Full Solder	See Page 106
	3/4 ST Half Solder	See Page 106
	Y Feed Thru Solder (.500)	See Page 106
	YSY Feed Thru Solder (.672)	See Page 106
	Z Lug over the Side (.609)	See Page 106
	J 602 Line to Line Jumper	See Page 107
	3786 Wire Clamp Screw	See Page 107
	2202 Stud	See Page 109
PSB	Phil-Slot Brass Screw	Consult C/S

Quick Connects: .032" x .250"

See pages 104-115 for terminal block accessories

