



COILED TELEPHONE CORDS

Coiled modular telephone cables suitable for handsets or standard extension cords. Extended lengths shown. (Ivory)

12-035-0 4P/4C 15' Length
Use -1 for Display Package

MODULAR 'T' ADAPTER



Modular 'T' adapter joins two cables to one jack.

12-210-0 6P/4C
12-213-0 6P/6C
12-214-0 8P/8C
Use -1 for Display Package



MODULAR TELEPHONE CORDS

Modular Cables with 6P/4C plugs on both ends (Ivory)

12-183-0 6P/4C 7' Length
12-185-0 6P/4C 15' Length
Use -1 for Display Package

SURFACE MOUNT WALL JACK (SINGLE)

Surface mount wall jack with adhesive back for easy mounting. Screw terminals for connections. Available in Ivory or White.



12-221-0 Ivory 6P/4C
12-221W-0 White 6P/4C
12-223-0 Ivory 6P/6C
12-223W-0 White 6P/6C
12-225-0 Ivory 8P/8C
12-225W-0 White 8P/8C
Use -1 for Display Package



MODULAR JOINER

Jack to jack joiner for connecting two cables.

12-202-0 6P/4C
12-203-0 6P/6C
12-204-0 8P/8C
Use -1 for Display Package

DOUBLE OUTLET SURFACE MOUNT WALL JACK

Surface mount wall jack with 2 outlets. Adhesive back and screws for mounting. Screw terminals for connections. Available in Ivory.



12-222-0 Ivory 6P/4C
Use -1 for Display Package



DATA JOINERS

12-203D-0 6P/6C
12-204D-0 8P/8C
Use -1 for Display Package

SINGLE OUTLET FLUSH MOUNT WALL PLATE



Telephone wall plates. Fits standard electrical box. Screw terminals.

12-231W-0 White 6P/4C
Use -1 for Display Package

Data joiners are connected from pin 1:1, 2:2, etc. Standard telephone joiners are cross connected - for example a 6P/6C is connected 1:6, 2:5, 3:4, 4:3, 5:2, 6:1.

MODULAR TELEPHONE DESIGNATIONS

The designation 6P/4C, 6P/6C, etc. refers to the number of contacts / number of wires used. The other common designations are:

4P/4C		for telephone handsets
6P/4C	RJ-11	Standard 4-conductor
6P/6C	RJ-12	Standard 6-conductor
8P/8C	RJ-45	Standard 8-conductor

MODE ELECTRONICS LTD.
211 - 2999 UNDERHILL AVE.,
BURNABY, B.C., CANADA, V5A 3C2
Phone: 604-435-6633
Fax: 604-435-8890
Toll Free: 1-800-663-4992
Web Site: www.mode-elec.com

DOUBLE OUTLET FLUSH MOUNT WALL PLATE



Double wall plates. Fits standard electrical box.

- 12-232-0** Ivory 6P/4C
- 12-232A-0** Almond 6P/4C
- 12-236-0** Ivory 8P/8C
Use -1 for Display Package
- 12-232W-0** White 6P/4C

MODULAR TELEPHONE PLUGS

Modular telephone plugs with 15µ" gold plated contacts.



- 12-253-0** 4P/4C
- 12-254-0** 6P/4C
- 12-256-0** 6P/6C
- 12-258-0** 8P/8C
Use -10 for Display Package
Use -50 for 50 Packs

MODULAR TELEPHONE PLUGS (for round cable)

Modular telephone plugs for round jacket cable with 15µ" gold plated contacts. **R** types are for stranded wire, **S** type is for solid wire and **U** type is for both stranded and solid wire.



- 12-254S-0** 6P/4C
- 12-254U-0** 6P/4C
- 12-256R-0** 6P/6C
- 12-256S-0** 6P/6C
- 12-256U-0** 6P/6C
- 12-258R-0** 8P/8C
- 12-258S-0** 8P/8C
- 12-258U-0** 8P/8C
Use -10 for Display Package
Use -50 for 50 Packs


- 12-254R-0** 6P/4C

PC MOUNT MODULAR JACKS

Printed circuit mount modular jacks. 6µ" gold plating.




12-264-0 & 12-266-0



- 12-264-0** 6P/4C
- 12-266-0** 6P/6C
- 12-288-0** 8P/8C

12-288-0



DELUXE MODULAR CRIMP TOOL



Deluxe crimp tool cuts, strips and crimps modular plugs.

- 12-306-1** 6P/4C & 6P/6C
- 12-308-1** 8P/8C

DELUXE MODULAR CRIMP TOOL



- 8P/8C (RJ45) precision crimper.
- Cuts and strips both flat and round modular cable.
- Extremely comfortable cushioned handles.
- Ratchet action with easy release.

12-309-1

MODULAR CRIMP TOOL



This versatile tool will crimp 4, 6 and 8 pin modular plugs. It also has a wire cutter and stripper built-in. Simple to use, extremely durable.

12-310-1

MODULAR TELEPHONE CABLE



28AWG stranded modular telephone cable. Available in silver-satin, beige or black jacket color.

- 12-402-0 Silver** 4-conductor 100'
- 12-403-0 Beige** 4-conductor 1000'
- 12-403-0 Silver** 4-conductor 1000'
- 12-603-0 Beige** 6-conductor 1000'
- 12-603-0 Silver** 6-conductor 1000'
- 12-805-0 Silver** 8-conductor 1000'

100' not on spools

The items shown in this catalog are normal stock items at Mode, but we can also source many additional products from reliable sources. If you have a requirement for a product not shown in this catalog, please contact us or your local distributor for price and delivery.

CATEGORY 5 PLUGS (8P/8C)

For round jacket/solid conductor cable.



13-101-0 * 30μ" Gold
13-102-0 * 50μ" Gold
 Use -5 for Display Package
 * Use -50 for 50 Packs

DOUBLE SURFACE MOUNT BOX



Double outlet surface mount box for 13-111-0 or 13-112-0 series jacks.



13-122-0 White
 Use -1 for Display Package

CATEGORY 5e KEYSTONE JACK



This jack requires no tooling. A color coded lift-up lid is used to place and insert the wires.



13-111E-0 5e white color
 Use -1 for Display Package

FLUSH MOUNT WALL PLATES



White flush mount wall plates for 13-111-0 or 13-112-0 series jacks.

13-131-0 for 1 jack - White
13-132-0 for 2 jacks - White
13-134-0 for 4 jacks - White
 Use -1 for Display Package

CATEGORY 5e KEYSTONE JACK



Standard 110 type IDC strips.



13-112E-0 5e white color
 Use -1 for Display Package

TV/PHONE PLATE



13-135WH-0 White
 Use -1 for Display Package

INSERTS FOR SURFACE MOUNT PLATES



Blank Insert-White

13-140-0 Bulk
13-140-2 Pkg (2)



ST Insert-White

13-141-0 Bulk
13-141-2 Pkg (2)



BNC Insert-White

13-142-0 Bulk
13-142-1 Pkg

SINGLE SURFACE MOUNT BOX



Single outlet surface mount box for 13-111-0 or 13-112-0 series jacks.

13-121-0 White
 Use -1 for Display Package

MODE ELECTRONICS LTD.
 211 - 2999 UNDERHILL AVE.,
 BURNABY, B.C., CANADA, V5A 3C2
 Phone: 604-435-6633
 Fax: 604-435-8890
 Toll Free: 1-800-663-4992
 Web Site: www.mode-elec.com

PATCH CORDS



Category 5e patch cords - available in 3', 7', 10', 14', and 25' lengths - colors - blue, yellow & grey.

- 13-161BL-0** 3' Long Blue
- 13-161GY-0** 3' Long Grey
- 13-162BL-0** 7' Long Blue
- 13-164GY-0** 14' Long Grey
- 13-164YL-0** 14' Long Yellow
- 13-165GY-0** 25' Long Grey
- 13-165YL-0** 25' Long Yellow

Use -1 for Display Package

CAT6 PATCH CORDS



Available in 3', 7', 10', 14', and lengths. Color is grey.

- 13-171GY-0** 3' Long
- 13-172GY-0** 7' Long
- 13-173GY-0** 10' Long
- 13-174GY-0** 14' Long

Use -1 for Display Package

COLOR CODED CABLE BOOTS



- 13-190BK-0** Black
- 13-190BL-0** Blue
- 13-190GR-0** Green
- 13-190GY-0** Grey
- 13-190RD-0** Red
- 13-190YL-0** Yellow

Use -4 for Display Package

Since modern twisted pair cabling must be expected to carry high signal rates, it is necessary to avoid stressing the wire. Tight 90-degree bends are not permissible, and any tie-wraps or other securing straps must not be cinched excessively tight. Care should be taken to avoid routing cables within 18 inches of electrical noise generating devices such as transformers and lighting ballasts. Please see our selection of hook and loop cable ties which are suitable for securing bundles of Cat 5 or Cat 5E cables.

CATEGORY 5 TOOLING



13-180-0 Bulk **13-180-1** Pkg.
Adjustable impact punch tool - using one of the inserts (below) this tool will insert and trim wires for the 13-112-0 & 13-113-0 keystone jacks.

13-186-1 Pkg.
Adjustable impact punch tool c/w 13-183-0 insert. Attractive display Package.



13-181-0 Bulk **13-181-1** Pkg.
Non-impact punch tool - using one of the inserts (below) this tool will insert and trim wires for the 13-112-0 & 13-113-0 keystone jacks.

13-187-1 Pkg.
Non-impact punch tool c/w 13-183-0 insert. Attractive display package.

INSERTS FOR 13-180-0 AND 13-181-0 PUNCH TOOL



13-182-0
For 66 type terminals- reversible punch or punch & cut



13-183-0
For 110 type terminals-reversible punch or punch & cut



13-184-0
For 66 & 110/88 type terminals. Punch only

Use -1 for Display Package

CABLE STRIP TOOL



13-185-0
Universal stripping tool for round or flat Cat 5 cable.
Use -1 for Display Package

ECONOMY PUNCH-DOWN TOOL AND CABLE STRIPPER



13-189-0
Disposable punch-down tool. Suitable for 5-6mm OD UTP/STP cable. For 110 type blocks.
Use -1 for Display Package

The Category 5 products shown on pages 5 and 6 are stocked items. We have access to many additional items such as patch panels, different styles of outlet boxes, etc. If you have a requirement for an item or items not shown on these pages, please contact us or your local Mode Distributor for price and delivery information.