

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0670688010](#)
Status: **Active**
Overview: [Consumer USB Products](#)
Description: Universal Serial Bus (USB), Shielded I/O, Type B Receptacle, Right Angle with Straight Tabs, Color Black, Gold (Au) Flash Plating, Tray Pack, Lead-Free

Documents:
[3D Model](#) [Product Specification PS-67998-0000 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General


Product Family I/O Connectors
Series [67068](#)
Application Wire-to-Board
Comments Single
Component Type Receptacle
Overview [Consumer USB Products](#)
Product Name USB 2.0
Type B
UPC 822348723010

Physical

Boot Color N/A
Circuits (Loaded) 4
Circuits (maximum) 4
Flammability 94V-0
Gender Receptacle
Lock to Mating Part Yes
Material - Plating Mating Gold
Material - Plating Termination Tin
Net Weight 4.169/g
Number of Rows 2
Orientation Right Angle
PC Tail Length 2.80mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Panel Mount No
Pitch - Mating Interface 2.50mm
Pitch - Termination Interface 2.50mm
Plating min - Termination 1.905µm
Polarized to Mating Part Yes
Polarized to PCB Yes
Ports 1
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating 0°C to +50°C
Termination Interface: Style Through Hole
Waterproof / Dustproof No
Wire Size AWG N/A

Electrical

Current - Maximum per Contact 1.5A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[67068](#) Series

Mates With

USB Type B Plug

Shield Type
Shielded
Voltage - Maximum

Full Shield
Yes
30V (RMS)

Material Info

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-67998-0000
SD-67068-003

This document was generated on 08/22/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION