

narrow your search

## Honeywell Sensing and Control

Search

11 TW1-7N

( Home : Products : TW » Switches » MICRO SWITCH™ Toggle Switches )

Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (21)

Technology

- Electromechanical (9301)
- Flexible Heaters (140)
- Microstructure (1486)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...



TW Series Toggle Switch, 1 pole, 3 position, Solder terminal, Locking Lever, Military Part Number MS27720-27-1N

*Actual product appearance may vary.*


Product Specifications

Circuitry/Operating action

Overview Specs Documentation

Product Type  
Lever Lock

Ampere/Voltage Range (Resistive Load)	0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc, 0.1 A to 5.0 A at 0.5 Vac to 115 Vac
Circuitry	SPDT
Action	3 position
Mounting	Bushing 15/32 in
Termination	Solder
MIL Spec. Number	MS27720-27 -1N
Lever Type	Locking
UL/CSA	L117: 5 A at 125 Vac
Comment	Fine silver contacts
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	TW



MICRO SWITCH™ Toggle Switch



Locked out of extreme position (Opposite keyway)

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site WGLA and WPMM XYR6000™

[find out more](#)

white papers

- ▶ Wireless Switches Offer Unlimited Benefit
- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters

Need help?

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)  
[Click here to contact us](#)

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



▶ Meet Dr. Larry

my links

- ▶ Login to iCOM
- ▶ Login to Rep/AD Portal
- ▶ Login to Digital University

News Center

- ▶ HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING
- ▶ HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES
- ▶ HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

**MICRO SWITCH Anniversary site**