



Extract from the online
catalog

UM 25-FLK20/FRONT/Q

Order No.: 2959515



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2959515>

VARIOFACE SLIM LINE, with screw connection and flat-ribbon cable
connector, for assembly at a right angle on NS 35/7.5, 20 positions



Commercial data

EAN	4017918086169
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.16218 KG
Catalog page information	Page 282 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
07/25/2006



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

General data

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per branch	0.8 A (data valid for 100% coincidence factor)
Number of positions	20

UM 25-FLK20/FRONT/Q Order No.: 2959515
http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2959515

Width	25 mm
Height	45 mm
Depth	177 mm
Ambient temperature (operation)	-10 °C ... 50 °C
Ambient temperature (storage/transport)	-10 °C ... 70 °C
Test voltage	500 V (50 Hz, 1 min)
Mounting position	Any
Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Pollution degree	2
Surge voltage category	II

Connection data

Connection 1	PCB connection
Connection in acc. with standard	IEC / EN
Type of connection	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3
Connection 2	Flat-ribbon cable connection
Type of connection	Pluggable

Certificates / Approvals



Certification

GOST

UM 25-FLK20/FRONT/Q Order No.: 2959515
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2959515>

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com